





15W 2"x1" Package 8:1 Ultra-Wide Input DC-DC Regulated Converter

SKA15W8 & DKA15W8 series



■ Features

- DIP 2"x1" package with industry standard pinout
- 8:1(9~75Vdc) ultra-wide input range
- Operating temperature range -40 ~ +90°C
- No minimum load required
- Comply to BS EN/EN55032 radiated Class A without additional components
- High efficiency up to 86%
- Protections: Short circuit (Continuous) / Overload / Over voltage / UVLO
- 3KVdc I/O isolation
- Remote ON/OFF control (By request)
- 3 years warranty

■ Applications

- Telecom/datacom system
- Wireless network
- Industrial control facility
- Instrument
- Analyzer
- Detector
- Data switch

■ GTIN CODE

MW Search: <https://www.meanwell.com/serviceGTIN.aspx>

■ Description

SKA15W8 and DKA15W8 series are 15W isolated and regulated module type DC-DC converter with DIP 2"x1" package. It features international standard pins, a high efficiency up to 86%, wide working temperature range -40~+90°C, 3KVdc I/P-O/P isolation voltage, compliance to BS EN/EN55032 radiated Class A without additional components, continuous-mode short circuit, overload, over voltage, input under voltage protection etc. The models account for 9~75Vdc 8:1 ultra-wide input range, and various output voltage, 3.3V/5V/9V/12V/15V/24V for single output and ±5V/±12V/±15V for dual outputs, which are suitable for all kinds of systems, Such as industrial control, telecommunication field, distributed power architecture, and so on.

■ Model Encoding

SKA 15 W8 -12

Output voltage (3.3/5/9/12/15/24Vdc, ±5/±12/±15Vdc)

8:1(9~75Vdc) Wide input voltage

Rated wattage

Series name { S:Single output
D: Dual output



15W 2"x1" Package 8:1 Ultra-Wide Input DC-DC Regulated Converter

SKA15W8 & DKA15W8 series

MODEL SELECTION TABLE							
ORDER NO.	INPUT			OUTPUT		EFFICIENCY (TYP.)	CAPACITOR LOAD (MAX.)
	INPUT VOLTAGE (RANGE)	INPUT CURRENT		OUTPUT VOLTAGE	OUTPUT CURRENT		
		NO LOAD	FULL LOAD				
SKA15W8-03	Nominal 12V, 24V,36V,48V,72V (9 ~ 75V)	10mA	679mA	3.3V	0~4000mA	81%	680μF
SKA15W8-05		10mA	744mA	5V	0~3000mA	84%	680μF
SKA15W8-09		10mA	727mA	9V	0~1666mA	86%	470μF
SKA15W8-12		15mA	727mA	12V	0~1250mA	86%	330μF
SKA15W8-15		15mA	727mA	15V	0~1000mA	86%	220μF
SKA15W8-24		15mA	727mA	24V	0~625mA	86%	100μF
DKA15W8-05		10mA	744mA	±5V	±0~1500mA	84%	*330μF
DKA15W8-12		15mA	727mA	±12V	±0~625mA	86%	*150μF
DKA15W8-15		15mA	727mA	±15V	±0~500mA	86%	*100μF

* For each output

File Name: SKA15W8, DKA15W8-SPEC 2026-04-13

SPECIFICATION

INPUT

VOLTAGE RANGE	9~75Vdc
SURGE VOLTAGE (100ms max.)	100Vdc
FILTER	Pi network
PROTECTION	Fuse recommended 5A Slow-Blow

OUTPUT

VOLTAGE ACCURACY	±2%
RATED POWER	15W
RIPPLE & NOISE	Note.2 150mVp-p max.
LINE REGULATION	Note.3 ±0.5%
LOAD REGULATION	Note.4 ±1% for 3.3Vdc output, ±0.5% for other output
CROSS REGULATION	±5% @ 25% ~ 100% load only dual output
SWITCHING FREQUENCY (Typ.)	300KHz (PWM)

PROTECTION

SHORT CIRCUIT	Protection type : Continuous, automatic recovery
OVERLOAD	110 ~ 230% Protection type : Recovers automatically after fault condition is removed
OVER VOLTAGE	Clamp by TVS diodes
UNDER VOLTAGE LOCKOUT (Typ.)	Start-up voltage: 8.8Vdc Shutdown voltage: 8Vdc

FUNCTION

REMOTE CONTROL (By request)	Power ON: R.C. ~ -Vin >2.5~30Vdc or open circuit ; Power OFF: R.C. ~ -Vin <1Vdc or short
-----------------------------	--

ENVIRONMENT

COOLING	Free-air convection
WORKING TEMP.	-40 ~ +90°C (Refer to "Derating Curve")
CASE TEMPERATURE	+110°C max.
WORKING HUMIDITY	5% ~ 95% RH non-condensing
STORAGE TEMP., HUMIDITY	-55 ~ +125°C, 10 ~ 95% RH non-condensing
TEMP. COEFFICIENT	±0.03% / °C (0 ~ 80°C)
SOLDERING TEMPERATURE	1.5mm from case of 3 ~ 5 sec./265°C max.
VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes

SAFETY & EMC (Note.5)

SAFETY STANDARDS	EAC TP TC 020/2011 approved
WITHSTAND VOLTAGE	I/P-O/P:3KVdc
ISOLATION RESISTANCE	I/P-O/P:1000M Ohms / 500Vdc / 25°C / 70% RH
ISOLATION CAPACITANCE (Typ.)	1000pF

EMC EMISSION	Parameter	Standard	Test Level / Note
	Conducted	BS EN/EN55032(CISPR32)	N/A
	Radiated	BS EN/EN55032(CISPR32)	Class A without additional components Class B with additional components
EMC IMMUNITY	Parameter	Standard	Test Level / Note
	ESD	BS EN/EN61000-4-2	Level 3, ±8KV air, Level 2, ±4KV contact
	Radiated Susceptibility	BS EN/EN61000-4-3	Level 2, 3V/m
	EFT/Bursts	BS EN/EN61000-4-4	Level 1, 0.5KV
	Surge	BS EN/EN61000-4-5	Level 2, Line-Line ±0.5KV
	Conducted	BS EN/EN61000-4-6	Level 2, 3V(e.m.f.)
	Magnetic Field	BS EN/EN61000-4-8	Level 1, 1A/m


OTHERS

MTBF	>860Khrs MIL-HDBK-217F(25°C)
DIMENSION (L*W*H)	50.8*25.4*11.2mm (2*1*0.44 inch)
CASE MATERIAL	Six-side shielded case
PACKING	29g ; 10pcs/per tube, 400pcs/40 tube/per carton

NOTE


1. All parameters are specified at normal input (24Vdc), rated load, 25°C 70% RH ambient.
 2. Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1μf & 47μf capacitor.
 3. Line regulation is measured from low line to high line at rated load.
 4. Load regulation is measured from 0% to 100% rated load.
 5. The final equipment must be re-confirm that it still meet EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on <http://www.meanwell.com>)
- ※ Product Liability Disclaimer : For detailed information, please refer to <https://www.meanwell.com/serviceDisclaimer.aspx>

Derating Curve



EMC Suggestion Circuit


※ Required external componets to meet BS EN/EN55032 radiated Class B emission as below:



Model No.	BS EN/EN55032 radiated Class B					
	F1	C1	C2	C3	C4	L1
SKA15W8 DKA15W8	Suggest 5A Slow-Blow Type	47μF/100V	2.2μF/100V 1210 MLCC	1000pF/5KV MLCC	1000pF/5KV MLCC	325μH Common Choke

Mechanical Specification


- All dimensions in mm(inch)
- Tolerance: $x.x \pm 0.5\text{mm}$ ($x.xx \pm 0.02"$)
 $x.xx \pm 0.25\text{mm}$ ($x.xxx \pm 0.010"$)
- Pin tolerance: $\phi 1 \pm 0.1\text{mm}$





Pin Assignment

Pin-Out		
Pin No.	SKA15W8 (Single output)	DKA15W8 (Dual output)
1	+Vin	+Vin
2	-Vin	-Vin
3	R.C.(By request)	
4	-Vout	-Vout
5	N.P.	Common
6	+Vout	+Vout

*N.P.: No pin



■ Packing

Standard Tube Packing	MPQ Per Tube (PCS)	One Tube G.W.	Max. Q'TY/ Carton(PCS)	One Carton G.W.
Unit : mm  Tube pattern  CARTON L620 x W230 x H230	10	378g	400	15.92Kg

■ Installation Manual

Please refer to : <http://www.meanwell.com/manual.html>