





features

- Designed to reduce noise at high frequencies
- Standard EIA packages: 1E, 1J, 2A, 2B
- Nickel barrier with solder overcoat for excellent solderability
- Magnetically shielded
- Marking: Black body color with no marking
- Products with lead-free terminations meet EU RoHS requirements

dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)			
	L	W	t	d
1E (0402)	.039±.004 (1.0±0.1)	.02±.004 (0.5±0.1)	.02±.004 (0.5±0.1)	.01±.004 (0.25±0.1)
1J (0603)	.063±.006 (1.6±0.15)	.031±.006 (0.8±0.15)	.031±.006 (0.8±0.15)	.014±.006 (0.36±0.15)
2A (0805)	.079±.008 (2.0±0.2)	.049±.008 (1.25±0.2)	.035±.008 (0.9±0.2)	.020±.012 (0.51±0.30)
2B (1206)	.126±.008 (3.2±0.2)	.063±.008 (1.6±0.2)	.043±.008 (1.1±0.2)	.020±.012 (0.51±0.30)

ordering information

New Part #	CZB	1E	G	T	TP	120	P
	Type	Size	Permeability Code	Termination Material	Packaging	Impedance	Tolerance
		1E 1J 2A 2B	F G S	T: Sn	TP: 7" paper tape (1E only - 10,000 pieces/reel) TD: 7" paper tape (1J, 2A - 4,000 pieces/reel) TE: 7" embossed plastic (2B - 3,000 pieces/reel)	2 significant figures + 1 multiplier	P: ±25%

For further information on packaging, please refer to Appendix A.

applications and ratings

Part Designation	Impedance @ 100MHz [†] (Ω)	DC Resistance Maximum ^{††} (Ω)	Allowable DC Current Maximum (mA)	Operating Temperature Range	
CZB1EGTTP100P	10	0.05	600	-55°C to +125°C	
CZB1EGTTP300P	30	0.30	500		
CZB1EGTTP600P	60	0.40	350		
CZB1EGTTP700P	70				
CZB1EGTTP800P	80				
CZB1EGTTP121P	120	0.50	300		
CZB1EGTTP221P	220	0.70	200		
CZB1EGTTP301P	300	0.80			
CZB1EGTTP451P	450	0.90			
CZB1EGTTP601P	600	1.00	150		
CZB1EGTTP102P	1000	1.50	100		
CZB1ESTTP100P	10	0.20	400		
CZB1ESTTP300P	30				
CZB1ESTTP600P	60	0.30			
CZB1ESTTP800P	80	0.40	300		
CZB1ESTTP121P	120				
CZB1ESTTP221P	220	0.60	200		
CZB1ESTTP301P	300	1.00			
CZB1ESTTP601P	600	1.20			
CZB1JGTTD300P	30	0.10	600		-55°C to +125°C
CZB1JGTTD600P	60	0.20			
CZB1JGTTD800P	80		0.25	400	
CZB1JGTTD101P	100				
CZB1JGTTD121P	120				
CZB1JGTTD141P	140				
CZB1JGTTD151P	150	0.30	300		
CZB1JGTTD181P	180				
CZB1JGTTD221P	220				
CZB1JGTTD301P	300	0.35	250		
CZB1JGTTD451P	450	0.40			
CZB1JGTTD601P	600	0.45			
CZB1JGTTD102P	1000	0.60	150		
CZB1JGTTD152P	1500	0.70			
CZB1JGTTD202P	2000	1.20	600		
CZB1JSTTD100P	10	0.10			
CZB1JSTTD300P	30	0.25	500		
CZB1JSTTD600P	60	0.30	400		
CZB1JSTTD800P	80				
CZB1JSTTD101P	100				
CZB1JSTTD121P	120	0.35	300		
CZB1JSTTD221P	220				
CZB1JSTTD301P	300				
CZB1JSTTD601P	600	0.65	200		
CZB1JSTTD102P	1000	0.80			
CZB2AFTTD110P	11	0.10	800	-55°C to +125°C	
CZB2AFTTD300P	30				
CZB2AFTTD500P	50				
CZB2AFTTD600P	60				
CZB2AFTTD800P	80	0.15	600		
CZB2AGTTD101P	100				

[†] Impedance test method: HP4291A

^{††} DCR test method: Keithley 580

For complete environmental specifications, please refer to www.koaspeer.com

applications and ratings (continued)

Part Designation	Impedance @ 100MHz † (Ω)	DC Resistance Maximum †† (Ω)	Allowable DC Current Maximum (mA)	Operating Temperature Range
CZB2AGTTD121P	120	0.25	600	-55°C to +125°C
CZB2AGTTD151P	150		500	
CZB2AGTTD201P	200	0.30	400	
CZB2AGTTD221P	220			
CZB2AGTTD301P	300			
CZB2AGTTD401P	400			
CZB2AGTTD501P	500			
CZB2AGTTD601P	600	0.25	500	
CZB2AGTTD601PV	600			
CZB2AGTTD102P	1000	0.40	300	
CZB2ASTTD110P	11	0.10	800	
CZB2ASTTD300P	30	0.20	600	
CZB2ASTTD600P	60			
CZB2ASTTD800P	80			
CZB2ASTTD121P	120	0.25	500	
CZB2ASTTD221P	220	0.30	400	
CZB2ASTTD301P	300	0.35		
CZB2ASTTD601P	600	0.40	300	
CZB2BFTTE190P	19	0.05	800	-55°C to +125°C
CZB2BFTTE300P	30	0.10	600	
CZB2BFTTE500P	50			
CZB2BFTTE600P	60			
CZB2BFTTE800P	80	0.20		
CZB2BFTTE101P	100	0.15		
CZB2BFTTE121P	120	0.20	500	
CZB2BFTTE151P	150	0.15		
CZB2BFTTE201P	200	0.20		
CZB2BFTTE221P	220			
CZB2BFTTE301P	300	0.30		
CZB2BFTTE501P	500	0.20		
CZB2BFTTE601P	600	0.40	400	
CZB2BGTTE202P	2000 @ 50MHz	0.70	300	
CZB2BSTTE601P	600	0.35	300	

[†] Impedance test method: HP4291A

^{††} DCR test method: Keithley 580

For complete environmental specifications, please refer to www.koaspeer.com