Pushing Performance
Since 1945

har-flex Board IDC 26p 600pcs per reel




Image is for illustration purposes only. Please refer to product description.

Part number	15 39 026 0601 234
Specification	har-flex Board IDC 26p 600pcs per reel
HARTING eCatalogue	https://harting.com/15390260601234

Identification

Category	Connectors
Series	har-flex®
Identification	Board IDC
Element	PCB transition connectors

Version

Termination method	Reflow soldering termination (SMT)
Connection type	PCB to cable
Number of contacts	26
Pack contents	Tape & reel

Technical characteristics

Conductor cross-section (AWG)	AWG 30
Contact rows	2
Contact spacing (termination side)	1.27 mm
Contact spacing (mating side)	0.635 mm
Rated current	1.18 A
Rated current	@ 85 °C
Clearance distance	0.4 mm
Creepage distance	0.4 mm
Insulation resistance	> 2.11 x 10^9 Ω
Contact resistance	<10 mΩ
Limiting temperature	-55 ... +125 °C

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Technical characteristics

Test voltage $U_{r.m.s.}$	0.91 kV
Isolation group	IIIa (175 ≤ CTI < 400)

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Sn over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	600
Net weight	2.745 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140837966
eCl@ss	27460201 PCB connector (board connector)
UNSPSC 24.0	39121415

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.