


REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	DEC 20/18	L.CHAN
B	PROPOSAL	DEC 24/18	L.CHAN



FRONT VIEW




SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE: ±0.05 (TOP VIEW)

AMPHENOL CANADA CORP
RoHS COMPLIANT
2011/65/EU RECAST



RECOMMENDED PANEL CUTOUT

MATERIALS:
PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V–0, COLOR: BLACK.

CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.
50 µ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 µ" [2.54 MICRONS]
MIN. MATTE–TIN OR GOLD FLASH ON CONTACT TAILS.

RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING AT 240°C MAXIMUM FOR 5 SEC MAXIMUM

PART NUMBER: RJE06–188–0X20

GOLD PLATING:
0 = GOLD FLASH
1 = 6 µ"
2 = 15 µ"
3 = 30 µ"
4 = 50 µ"

UNLESS SPECIFIED OTHERWISE	DRAWN HANSON.C	DATE DEC 20/18	Amphenol Canada Corp. Commercial Products
PRIMARY UNITS MILLIMETER	CHECKED L.CHAN	DEC 20/18	
SECONDARY INCH	M.E. APP'D		TITLE: RJE06 SERIES, 8 POSITION 8 CONTACT, VERTICAL MOUNT, UNSHIELD WITH FLANGE – RoHS COMPLIANT
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE ±0.38	ENG. REL. NO.		DWG. NO. P–RJE06–188–0X20 REV B
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES ±0.20	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1
ANGULAR DEGREES ±1.0°			

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.