

PRODUCT NUMBER

89361-YXXSLF


LEAD FREE, RoHS COMPLIANT

SEE NOTE 4


STRAIN RELIEF OPTION, SEE NOTE 5

TOTAL NB OF POSITIONS, SEE SHEET 2


FEATURES, SEE SHEET 2



INDICATES POS 1
SEE NOTE 6



VIEW WITHOUT COVER




mat'l. code SEE NOTE				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family MINITEK IDC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title 2.00mm IDC 0.2µm Au			
K	F06-0211	LMU	06.07.03	angles	linear					
L	F07-0215	LMU	07.06.12							
M	F08-0218	JCO	08.09.09	±2°						
N	F09-0081	JCO	09.08.27	dr	L.MULIN	07.03.20	Amphenol FCI			
P	F-21434	BVE	15.07.16	engr	J.COMPAGNON	07.03.20				
R	F-279781	DDE	26.02.27	chr						
				appd	J.COMPAGNON	07.03.20				
sheet index	revision sheet	R	R				dwg no 89361			
		1	2				sheet 1 of 2			
							size A3			
							type CUSTOMER			
							Drawing			

PDS: Rev :R

STATUS:Released Printed: Feb 28, 2026

PRODUCT SIZE	TOTAL NB OF POS	DIM "A"	DIM "B"	DIM "C"	STRAIN RELIEF OPTION
89361-X06LF	2x 3	4	10.6	5	YES
-X08LF	2x 4	6	12.6	7	YES
-X10LF	2x 5	8	14.6	9	YES
-X12LF	2x 6	10	16.6	11	YES
-X14LF	2x 7	12	18.6	13	YES
-X16LF	2x 8	14	20.6	15	YES
-X18LF	2x 9	16	22.6	17	YES
-X20LF	2x 10	18	24.6	19	YES
-X22LF	2x 11	20	26.6	21	NOT TOOLED
-X24LF	2x 12	22	28.6	23	YES
-X26LF	2x 13	24	30.6	25	YES
-X28LF	2x 14	26	32.6	27	NOT TOOLED
-X30LF	2x 15	28	34.6	29	YES
-X34LF	2x 17	32	38.6	33	YES
-X36LF	2x 18	34	40.6	35	NOT TOOLED
-X40LF	2x 20	38	44.6	39	YES
-X44LF	2x 22	42	48.6	43	YES
-X48LF	2x 24	46	52.6	47	YES
-X50LF	2x 25	48	54.6	49	YES



NOTES :

- 1 - MATERIAL : TERMINAL PHOSPHORE BRONZE
BASE AND COVER : PBT GLASSFILLED UL 94V-0 BLACK
- 2 - PLATING : GOLD 0.2µm Au MIN ON CONTACT AREA
NICKEL 1.27µm MIN UNDERPLATING ALL OVER
- 3 - RECOMMENDED CABLE SIZE : AWG28, STRANDED
- 4 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.
- 5 - S= STRAIN RELIEF ACCESSORY, SEE TABLE FOR AVAILABILITY,
OMIT LETTER FROM PARTNUMBER IF NOT APPLICABLE.
- 6 - SIZE 2 x 3 AND 2 x 4 WILL NOT HAVE POSITION #1
TRIANGLE SHOWING

				AVAILABILITY
89361-7XX			○	FROM 2x3 POS UP TO 2x17
89361-3XX		○		FROM 2x17 POS UP TO 2x25
89361-1XX	○			FROM 2x3 POS UP TO 2x25
PRODUCT CODE	WITHOUT CENTRAL KEY	WITH CENTRAL KEY	WITH CENTRAL KEY AND FRICTION LATCH BUMP	

mat'l. code SEE NOTE				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK IDC			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title 2.00mm IDC 0.2µm Au				
K	F06-0211	LMU	06.07.03	angles	linear	x.X ±0.3			dwg no 89361 sheet 2 of 2 size A3				
L	F07-0215	LMU	07.06.12			x.XX ±0.13							
M	F08-0218	JCO	08.09.09			x.XXX ±0.05							
N	F09-0081	JCO	09.08.27	dr	L.MULIN		07.03.20		type CUSTOMER Drawing				
P	F-21434	BVE	15.07.16	engr	J.COMPAGNON		07.03.20						
R	F-279781	DDE	26.02.27	chr	J.COMPAGNON		07.03.20						
				appd	J.COMPAGNON		07.03.20						
sheet index		revision sheet											
											</		