

8LT, 8ST & 8D Series Reinforced Sealing



38999 Connector with Reinforced Sealing

Resin sealed for harsh environment applications. Up to 1000 times higher sealing than standard version.

Wide availability ■ All 38999 layouts.
Aluminum, including RoHS Black Zinc Nickel.
Composite for ultra low weight.
Titanium or stainless steel for outdoor application.

Fully intermateable ■ 8LT with MS27466 or HE308.
8ST with VG96912 or JN1003.
8D with D38999, EN3645 or BACC63CT/DB.

Temperature ■ Fast temperature change: from -55°C to 125°C.
Compatible with wave or iron soldering.

Contacts ■ PC tail or solder contacts.
Male or female contacts.
Tin plated version available.
Shoulderless contact available, consult us.



Not QPL registered.



Description

- Reinforced sealed receptacle with male or female straight PC tail contacts
- Strong sealing performance: 10^{-7} atm.cm³/s
- Designed for unpressurized area
- 125°C max (operational temperature)
- 100 % scoop proof
- Full RoHS solution
- High density connectors
- Weight saving compared to hermetic version
- Other SOURIAU ranges on request

Technical features

Mechanical

- **Shell plating:**
 - . 8LT & 8ST aluminum shell:
 - . Black zinc nickel (Z)
 - . Olive drab cadmium (B)
 - . Nickel (F)
 - . 8D aluminum shell:
 - . Black zinc nickel (Z)
 - . Olive drab cadmium (W)
 - . Nickel (F)
 - . 8D composite shell:
 - . Olive drab cadmium (J)
 - . Nickel (M)
 - . 8D stainless steel shell:
 - . Nickel (S)
 - . Passivated (K)
 - . 8D titanium shell:
 - . Nickel (TF)
 - . Without plating (TT)
- **Insulator:** Thermoplastic
- **Interfacial seal:** Silicone elastomer
- **Contacts:** Copper alloy
- **Contacts plating:** Gold over nickel plated
- **Endurance:**
 - 500 mating/unmating operations

Electrical

- **Contact resistance:**

Contacts size	26	22	20	16	12	8	4
Resistance mΩ	16	14.6	7.3	3.8	3.5	3	2

- **Shielding:**
 - . 8LT: . 90db - 100MHz
 - . . 50db - 10GHz
 - . 8ST: . 70 db - 100MHz
 - . 8D: . F; S; TF: 65db - 10GHz
 - . . F; Z; W; J; M: 85db - 1GHz
 - . . Z; W: 50db - 10GHz
 - . . K; TT: 45db - 10GHz
- **Shell continuity:**
 - . 8LT: . Z; B: 2.5mΩ
 - . . F: 1mΩ
 - . 8ST: . Z; B: 2.5mΩ
 - . . F: 1mΩ
 - . 8D: . F; TF; S: 1mΩ
 - . . Z; ZC; W: 2.5mΩ
 - . . J; M: 3mΩ
 - . . JVS: 5mΩ
 - . . TT; K: 10mΩ

Environmental

- **Temperature range:** -55°C +125°C
- **Sealing (initial):** 10^{-7} atm.cm³/s
- **Salt spray:**
 - . 8LT: . B; Z: 500h
 - . . F: 48h
 - . 8ST: . B; Z: 500h
 - . . F: 48h
 - . 8D: . F; S; TF: 48h
 - . . Z; W; JVS; TT; K; S: 500h
 - . . J; M: 2000h

Ordering information

8LT part number

Basic Series	8LTR	0	C	09	Z	35	P	N
Shell style 0: Square flange receptacle 1: In line receptacle 2: Short square flange receptacle not accepting backshell 3: Square flange receptacle, rear mounting 7: Jam nut receptacle								
Type C: Receptacle with short PC tail (male and female #22D, #20, #16) L: Connector with long PC tail (male and female #22D) S: Connector with specific PC Tail (male and female #22D) M: Connector with medium PC tail (male #22D) P: Connector with solder cup: . Pin: #22D & #16; Socket: #12 . Socket: #22D & #16; Pin: #12 - Please consult us								
Shell size 09, 11, 13, 15, 17, 19, 21, 23, 25								
Plating B: Olive green cadmium F: Nickel Z: Black zinc nickel								
Contact layouts See page 5								
Contact type P: Male S: Female								
Orientation N, A, B, C, D (Orientation B & C not developed for shell size 9)								

8ST part number

Basic series	8STR	0	C	10	Z	35	P	N
Shell style 0: Square flange receptacle 1: In line receptacle 2: Square flange receptacle, not accepting backshell 3: Square flange receptacle, rear mounting 7: Jam nut receptacle								
Type L: Connector with long PC tail contacts M: Connector with medium PC tail contacts C: Connector with short PC tail contacts								
Shell size 08, 10, 12, 14, 16, 18, 20, 22, 24								
Plating Z: Black zinc nickel F: Nickel G: Olive green cadmium								
Contact layouts See page 5								
Contact type P: Pin S: Socket								
Orientation N, A, B, C, D (Orientation B & C not developed for shell size 8)								

Ordering information

8D part number

Basic Series:	8DR	0	C	09	Z	35	P	N
Shell type: 0: Square flange receptacle 1: In line receptacle (8D aluminum only) 7: Jam nut receptacle (except 8D Composite)								
Contact type: C: Receptacle with short PC tail (male and female #22D, #20, #16, #12) L: Connector with long PC tail (male and female #22D) S: Connector with specific PC Tail (male and female #22D) M: Connector with medium PC tail (male #22D) P: Connector with solder cup: . Pin: #22D, #20 & #16; Socket: #12 . Socket: #22D, #20 & #16; Pin: #12 - Please consult us								
Shell size 09, 11, 13, 15, 17, 19, 21, 23, 25								
Aluminum plating: F: Nickel Z: Black zinc nickel W: Olive drab cadmium								
Composite plating: J: Olive drab cadmium M: Nickel								
Stainless steel plating: K: Passivated S: Nickel								
Titanium plating: TT: Without plating TF: Nickel								
Contact layout See page 5								
Contact type: P: Male S: Female								
Orientation N, A, B, C, D, E								

Double flange receptacle available, please consult us.

Receptacle with integrated clinch nuts or helicoils available, please consult us.


Contacts without shoulder available, please consult us.

Dimensions

See «8LT Series / MIL-DTL-38999 Series I», «8ST Series / VG96912 & JN1003» and «8D Series / MIL-DTL-38999 Series III» catalogs.

Contact layouts

For C or L contact type. For other contact type or layouts, please consult us.



For further information contact us at technical.emear@souriau.com (Europe - Asia - Africa)
technical.americas@souriau.com (North America)
 or visit our web site www.souriau.com