



Part Number : [1202530464](#)
Product Description : Contrinex Inductive Sensor,
3mm Diameter Smooth Housing, 0.6mm Operating
Distance, Embeddable, PNP, NO, 0.2m 3-wire PUR
Cable, 3-pin M8 Connector, 22mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric
Sensors
Engineering Number : DW-AV-603-03-276



Documents & Resources

Specifications

[1202530458-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, 3mm Diameter Smooth Housing, 0.6mm Operating Distance, Embeddable, PNP, NO, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 22mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130067893

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 5000 Hz

Physical

Connection	Cable (PUR 0.2m, 3-wire), Connector (M8, 3-pin)
Length	22mm
Material - Housing	Stainless Steel
Material - Sensing Face	Polyester
Mounting Style	Embeddable

Operating Distance	0.6mm
Output	NO
Sensor Housing Size	3mm dia. (smooth)
Temperature Range - Operating	-25° to +70°C

This document was generated on Sep 10, 2025