C4532X7R2E224K230KA

TDK Item Description : C4532X7R2E224KT****

Lead Free | Halogen Free | REACH | RoHS COMPLIANT

Characterization Sheet (Multilayer Ceramic Chip Capacitors)

Application & Main Feature

Commercial Grade (Mid Voltage (100 to 630V))

Series

C4532 [EIA CC1812]



Dimensions

L	4.50mm +/-0.4mm
W	3.20mm +/-0.4mm
T	2.30mm +/-0.2mm
B	0.20mm Min.
G	

Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

Rated Voltage

2E (250Vdc)

Capacitance

220nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

3% Max.

Insulation Resistance

2.27Gohm Min.

AEC-Q200

Not Applicable

DC Bias Characteristic



|Z|, ESR vs. Freq. Characteristics



Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



TDK

All specifications are subject to change without notice.

January 4, 2016

Downloaded from Arrow.com.