



NOTES:

1. RESISTANCE @ 25°C : 10KΩ±1%
2. BETA VALUE (0/50°C) : 3964K±1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +135°C.
4. DISSIPATION FACTOR : 1.5mW/°C
5. THERMAL TIME CONSTANT : LESS THAN 3SECONDS IN WATER
- 6.INSULATION RESISTANCE : 10MΩ AT 100 VDC

FUNCTIONAL SYMBOLS = 0 = 0 = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex NTC EPOXY - 3964 25MM 10K 1%					
	mm		NTS										
	GENERAL TOLERANCES (UNLESS SPECIFIED)												
	ANGULAR TOL ± °												
	4 PLACES		±		EC NO: 657230			PRODUCT CUSTOMER DRAWING					
	3 PLACES		±		DRWN: RAVIKM 2021/03/04								
	2 PLACES		±		CHK'D: RBBHASKAR 2021/03/05								
	1 PLACE		±		APPR: RBBHASKAR 2021/03/05			DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION
	0 PLACES		±		INITIAL REVISION:			2152743603			PSD	000	A
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A3-SIZE		215274		2152743603		OTS		1 OF 1	