

T&B

FLEXSTRIP* JUMPERS.

+CONDUCTOR PITCH "A"	MARGIN C (min.)	THICKNESS D (MAX.)	PIN DIAMETER E ±0,025 (±.001")	NUMBER OF CONDUCTORS
Cat.Ref. mm (inch)	mm (inch.)	mm (inch.)	mm (inch.)	min. max.
1 1,27 .050"	0,25 .010"	0,64 .025"	0,320 .0126"	2 - 30
6 1,90 .075"	0,38 .015"	0,84 .033"	0,404 .0159"	2 - 30
2 2,54 .100"	0,51 .020"	0,84 .033"	0,511 .0201"	2 - 30
3 3,18 .125"	1,52 .060"	0,84 .033"	0,511 .0201"	2 - 25
4 3,81 .150"	1,52 .060"	0,84 .033"	0,511 .0201"	2 - 20
5 5,08 .200"	1,52 .060"	0,84 .033"	0,511 .0201"	2 - 15

Dimensions are shown in mm (inches.)
+ Tolerance on Pitch ±0,25 (0.01") non-cumulative.


INSULATION LENGTH B ±1.57 (±0.062")		
mm	(inch)	Cat. Ref.
25.4	1	1
38.1	1½	1.5
50.8	2	2
63.5	2½	2.5
76.2	3	3
88.9	3½	3.5
101.6	4	4
114.3	4½	4.5
127	5	5
139.7	5½	5.5
152.4	6	6

PROPERTIES :-

Insulation Material - Nomex#
Temperature Rating - 105°C
Current Rating - 2 amps
U.L. Style Number - 5188

NOTES:-

* Trademark of Thomas & Betts Corporation
* Registered trademark of E.I. Du Pont de Nemours



CATALOGUE NUMBERING SYSTEM

Product Code — FSN-XXA-X
Conductor Pitch (see table for ref' N°) —
Insulation Length (see table for ref' N°) —
Number of Conductors (see table for max' number) —
Straight Pin —

EXAMPLE:-


FSN - 22A - 15

FSN - Flexstrip Jumper With Nomex Insulation
2 - Conductor Pitch 2.54 (0.100)
2 - Insulation Length 50.8 (2)
A - Straight Pin
15 - Number of Conductors 15

T&B THOMAS & BETTS INTERNATIONAL
EUROPEAN ENGINEERING DIVISION

DRG. N°
3S-10018

IMPERIAL DIMENSIONS
SHOWN THUS []
TOLERANCES
-0000 EQUALS -0002
-000 EQUALS -003
-00 EQUALS -015



THIRD ANGLE PROJECTION

MATERIAL		PART NAME	
HEAT TREAT		PRODUCT CODE	
FINISH		TOLERANCES UNLESS OTHERWISE SPECIFIED	
SCALE		FSN-11A-10	
DR.		tyco	
CH.		1437130-4	
APP.		Electronics REV 0 SHT 1 of 1	
REV	DESCRIPTION	DATE	BY