

Search...

SPC5603BK0MLQ6 :Part Detail

General Information	Package Information	Environmental and Compliance Information	Manufacturing Information	Ordering Information
Operating Characteristics				

General Information

Part Number	SPC5603BK0MLQ6
Description	"NXP 32-bit MCU, Power Arch core, 384KB Flash, -40/125degC, Automotive Grade, QFP 144, 64MHz,"
Product Line	G9F564BA
PTI	JBDC
Material Type	Tested Packaged Device
Life Cycle Description (code) (/webapp/sps/site/eialink.jsp)	PRODUCT STABLE GROWTH/MATURITY
Status	Active
Application/Qualification Tier (/webapp/sps/site/aqtlink.jsp?type=pop_up)	AUTO; >=10 YEARS APPLICATION LIFE

Package Information

Package Type and Termination Count	LQFP 144
Package Description and Mechanical Drawing	LQFP 144 20SQ1.4P0.5 C90
Device Weight(g)	1.31910
Package Length (nominal)(mm)	20.000
Package Width (nominal)(mm)	20.000
Package Thickness (nominal)(mm)	1.500
Maximum Height Above Board(mm)	1.600
Tape & Reel	No

Environmental and Compliance Information

Pb-Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PBFREE_INFO&type=pop_up)	
RoHS Compliant (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_INFO&type=pop_up)	
Halogen Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=HALOGEN_FREE_INFO)	Yes
Material Composition Declaration (MCD) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_MCD&type=pop_up)	Download MCD Report  (/mcds/SPC5603BK0MLQ6.pdf) Download MCD Report  (/mcds/SPC5603BK0MLQ6.xls)
RoHS Certificate of Analysis (CoA) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_COA&type=pop_up)	Contact Us (https://nxpcommunity.force.com/community/communityContactSupport)
2nd Level Interconnect (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PLATING_INDICATOR_INFO)	e3
Moisture Sensitivity Level (MSL)	3
Floor Life	168 HOURS
Peak Package Body Temperature (PPT)(°C)	260
Maximum Time at Peak Temperature (s)	40

Number of Reflow Cycles	3
REACH SVHC	NXP REACH Statement (/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf)
UL94 (plastics flammability test)	V0;Burning stops within 10 seconds on a vertical specimen;no drips allowed

Manufacturing Information

Micron Size(μm)	.09
-----------------	-----

Ordering Information

Minimum Package Quantity (MPQ)	60
MPQ Container	TRAY
Exempt from Minimum Delivery Value	No
Preferred Order Quantity (POQ)	300
POQ Container	BOX
Leadtime (weeks)	16
Export Control Classification Number (US)	3A991A2
Harmonized Tariff (US) Disclaimer (/webapp/sps/site/harmTariffDisclaim.jsp)	8542.31.0000
CCATS Document	-
ENC Status	-
Other Trade Compliance Documents	-
Budgetary Price excluding tax(US\$) (/webapp/sps/site/bplink.jsp) Change Currency	-
Order	

Operating Characteristics

Sample Exception Availability	N
-------------------------------	---

ABOUT NXP

Investors (<http://investors.nxp.com/phoenix.zhtml?c=209114&p=irol-irhome>)
Partners (<http://www.nxp.com/webapp/connect/memberDirSearch.sp>)
Careers (<http://www.nxp.com/about/careers-at-nxp:CAREERS>)

RESOURCES

Mobile Apps (<http://www.nxp.com/about/nxp-mobile-applications:MOBILE>)
Press, News, Blogs (<http://media.nxp.com>)
Contact Us (<http://www.nxp.com/pages/contact-us:CONTACTUS>)

FOLLOW US

(<https://twitter.com/NXP>) (<http://www.linkedin.com/company/nxp-semiconductors>) (<https://www.facebook.com/NXPsemi>)

(<https://contact.nxp.com/Subscription-Center>)

News 16 Feb 2017

Getting to the Root of Trust
Read More (<http://blog.nxp.com/security/getting-to-the-root-of-trust>)

