


REV. 0
DCO 142658

COIL: @ 25°C


RESISTANCE	140 OHMS ± 10%
NOMINAL VOLTAGE	9.0 VDC
MUST OPERATE	4.4 VDC
MUST RELEASE	2.6 VDC MAX. 0.5 VDC MIN.

ENVIRONMENT:

VIBRATION	10	CPS TO	3000	CPS @	30 g's
SHOCK	75	g's	6	MS. DURATION	
TEMPERATURE	-65	°C TO	+125	°C	

NOTES: OPERATE & RELEASE 4 MS MAX.
CONTACT STABILIZATION TIME 25 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2 AMPS 28 VDC RESISTIVE 50,000 OPERATIONS

DR. PBB 1/25/01 CK. TLG 01-25-01

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/13-075 REV.

"3SBC" RELAY

3SBC2020A2

SUPERSEDED
NOT the LATEST REVISION

Downloaded from Arrow.com.