

Part Number : 2162921013
Product Description : Standard .093" Male-to-Standard .093" Male Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, Tin (Sn) Plating, 1 Circuit, Natural
Series Number : 216292
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2162921013_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Melamine per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216292
Description	Standard .093" Male-to-Standard .093" Male Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, Tin (Sn) Plating, 1 Circuit, Natural
Application	Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Standard 093"-to-Standard 093"
Product Name	Standard .093"
Type	Discrete Wire Assembly
UPC	193264735716

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	600.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Natural
Gender	Male-Male

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	22.021/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	6.70mm
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Size (AWG)	14

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing with Positive Latch, UL 94V-0, 1 Circuit	19091016
2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing with Positive Latch, UL 94V-2, 1 Circuit	19091019

Downloaded from Arrow.com.