


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
3/05/10	J	Updated PCB Layout	T.B.	B.S.	
4/25/14	K	Updated to ROHS 2 Compliant	T.B.	B.S.	
01/27/17	L	Updated UL File number	T.B.	B.S.	
10/18/19	M	Added weight of the part	T.B.	B.S.	



SPECIFICATIONS:

- * Holder material- Zenite 30% glass reinforced Liquid Crystal Polymer resin, UL File No. E344082, UL94V-0
- * Color: Off White
- * Contacts : 0.020" thick PHOS-BRONZE, GOLD FLASH
- * Temperature range: -40°C to +280°C
- * Vibration Test: 10-50-10 Hz swept in 60 seconds
X,Y,Z direction: 1 hour each direction
- * Result: No dislodgement of the cell or damage
No discontinuity over 10 micro-seconds
- * Shock Test: Half sine wave acceleration 150G. 6 ms
3 shock pulses each direction per axis, total of 18 pulses
- * Result: No evidence of physical damage
- * ROHS COMPLIANT

Weight: 1.25g

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
decimal ±.5 (.020)			Scale	Drawn By B.S.
			Approved By T.B.	
Fractional ± .8 (.030)	Title SURFACE MOUNT BATTERY HOLDER FOR CR2032			
Angular ± 3°	Date 10/18/19	Drawing Number BU2032SM-HD-G		