

Terminal Part Number: 12034172

Surface Plating: SN

Material Thickness [mm]: 0,41

Cross Section [mm²]: 3,00 | 5,00

Cable Type codes: 1005

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 3,00 - 4,07

Seal(s): 15324989 | 15324990

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 3,00 / 15324989		3,13	250	2,10	0,05	3,70	0,10	6,80	0,20	6,70	0,20
1005 5,00 / 15324990		3,89	300	2,20	0,05	3,70	0,10	6,80	0,20	6,70	0,20

Cable type code legend:

1005:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, PVDF, XLPE

Insul. Wall Designator: THIN



Terminal Part Number: 12034172
Surface Plating: SN
Material Thickness [mm]: 0,41
Cross Section [mm²]: 3,00 | 5,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office



Cable Type codes: 1007
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 3,45 - 4,70
Seal(s): 15324989 | 15324990

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1007 3,00 / 15324989		3,63	250	2,10	0,05	3,70	0,10	6,80	0,20	6,70	0,20
1007 5,00 / 15324990		4,45	300	2,20	0,05	3,70	0,10	6,80	0,20	6,70	0,20

Cable type code legend:

1007:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPA/PVDF, XLPE
Insul. Wall Designator: REGULAR



Terminal Part Number: 12034172
Surface Plating: SN
Material Thickness [mm]: 0,41
Cross Section [mm²]: 3,00 | 5,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office



Cable Type codes: 1009
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 4,00 - 5,33
Seal(s): 15324990 | 15324987

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1009 3,00 / 15324990		4,13	250	2,10	0,05	3,70	0,10	6,80	0,20	6,70	0,20
1009 5,00 / 15324987		5,07	300	2,20	0,05	3,70	0,10	6,80	0,20	7,70	0,20

Cable type code legend:

1009:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE
Insul. Wall Designator: SPECIAL



Terminal Part Number: 12034172
Surface Plating: SN
Material Thickness [mm]: 0,41
Cross Section [mm²]: 2,50 | 4,00

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2005
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,70 - 3,80
Seal(s): 12052452

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2005 2,50 / 12052452		2,85	406	2,00	0,05	3,60	0,10	6,15	0,20	6,90	0,20
2005 4,00 / 12052452		3,60	418	2,15	0,05	3,65	0,10	6,60	0,20	6,90	0,20

Cable type code legend:

2005: FLR2X (SAAB C)
Industry Designator: ISO
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE
Insul. Wall Designator: THIN



Terminal Part Number: 12034172
Surface Plating: SN
Material Thickness [mm]: 0,41
Cross Section [mm²]: 2,50 | 4,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 2010
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,60 - 3,70
Seal(s): 15327864 | 12052452

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 2,50 / 15327864		2,80	89	1,95	0,05	3,65	0,10	6,50	0,20	6,55	0,20
2010 2,50 / 12052452		2,80	375	2,00	0,05	3,65	0,10	6,30	0,20	6,95	0,20
2010 4,00 / 12052452		3,45	392	2,15	0,05	3,65	0,10	6,65	0,20	6,95	0,20
2010 4,00 / 15327864		3,45	312	2,15	0,05	3,70	0,10	6,85	0,20	6,70	0,20

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 12034172

Surface Plating: SN

Material Thickness [mm]: 0,41

Cross Section [mm²]: 2,50

Cable Type codes: 2017

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 2,60 - 3,00

Seal(s): 12052452

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2017 2,50 / 12052452		2,80	394	2,00	0,05	3,65	0,10	6,30	0,20	6,85	0,20

Cable type code legend:

2017: FLR41X-B, FLRY-A

Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: SN

Insul. Material: PA, PP, PVC, XLPE

Insul. Wall Designator: THIN

