



Part Number : [1200668832](#)

Product Description : Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 4 Poles, A-Coded, Male (Straight) to Female (90°), 22 AWG, Black TPU WSOR Cable, 3.0m (9.84') Length

Series Number : 120066

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 884031B30M030



Documents and Resources

Drawings


[1200668832_sd.pdf](#)

Specifications

[TS-120065-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 4 Poles, A-Coded, Male (Straight) to Female (90°), 22 AWG, Black TPU WSOR Cable, 3.0m (9.84') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	887191555249

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.10mm (.201")
----------------	----------------

Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	125.600/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	22

This document was generated on Dec 16, 2025