


Part Number : 901210133
Product Description : C-Grid III PCB Header, 2.54mm Pitch, Through Hole, Single Row, Right-Angle, 13 Circuits, Tin (Sn) Plating
Series Number : 90121
Status : Active
Product Category : PCB Headers and Receptacles

Documents and Resources

Drawings

901210133_sd.pdf

PK-90120-100-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

901190001-AS-000.pdf

PS-99020-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	90121
Description	C-Grid III PCB Header, 2.54mm Pitch, Through Hole, Single Row, Right-Angle, 13 Circuits, Tin (Sn) Plating
Application	Board-to-Board, Wire-to-Board
Component Type	PCB Header
Product Name	C-Grid III
UPC	800753713734

Agency

UL	E29179

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	350V AC/DC

Physical

Breakaway	Yes
Circuits (Loaded)	13
Circuits (maximum)	13

Downloaded from Arrow.com.

Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Mounting Style	Through Hole
Net Weight	0.975/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.90mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	3.000µm
Plating min - Termination	3.000µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	Unshrouded
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE

Downloaded from Arrow.com.

Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid III Vertical Single Row PC Board Connectors	90147
C-Grid III Right-Angle Single Row PC Board Connectors	90148
C-Grid III Modular Single Row Crimp Housings	90123

Downloaded from Arrow.com.