



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

1N270 Germanium Diode Optimized for Radio Frequency Response

Description:

The 1N270 is a Germanium Diode in a DO-7 type glass package that can be used in many AM, FM and TV-IF applications, replacing point contact devices.

Features:

- DO-7 Glass Package
- Lower Leakage Current
- High Mechanical Strength

Applications:


- AM/FM Detectors
- Radio Detectors
- FM Discriminators
- TV Audio Detectors
- RF Input Probes
- TV Video Detectors

Absolute Maximum Ratings: ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Peak Inverse Voltage, PIV	100V
Surge Current ($t = 1$ second), I_{FSM}	500mA
Average Rectified Forward Current, I_O	40mA
Peak Operating Current, I_{OS}	325mA
Operating Junction Temperature, T_J	-65° to $+90^{\circ}\text{C}$
Storage Temperature Range, T_{stg}	-65° to $+90^{\circ}\text{C}$

Electrical Characteristics: ($T_A = +25^{\circ}\text{C}$, unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage Drop	V_F	$I_F = 200\text{mA}$	—	—	1	V
Breakdown Voltage	PIV	$I_R = 1\text{mA}$	100	—	—	V
Reverse Leakage	I_R	$V_R = 50\text{V}$	—	—	100	μA
Junction Capacitance	C_J	$V_R = 1\text{V}$, $f = 1\text{MHz}$	—	0.8	—	pF



Color Band Denotes Cathode