










REV.	DATE	DESCRIPTION
A	05/10/01	MODIFY INSULATOR/CONTACT PIN DIMENSIONS
B	01/30/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex			
8	HEAT SHRINK TUBE			1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	DRAWN G.R.S.	01/30/04	PART DESCRIPTION SMA CRIMP JACK (FOR RG-178B/U, 196A/U CABLE)		
7	FERRULE	COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED				
6	HEX NUT	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	ISSUED				
5	BARREL	BRASS	GOLD	1		SHEET 1 OF 1				
4	INSULATOR	TEFLON	NATURAL	1		CAD FILE		PART NO. 132279		
3	CONTACT PIN	BER. COPPER	GOLD	1				DWG. NO. 132279.DWG		
2	INSULATOR	TEFLON	NATURAL	1				REV. B		
1	BODY	BRASS	GOLD	1				SIZE A		
								SCALE NA		