


Data Sheet | Item Number: 787-880

Capacitive buffer module; 24 VDC input voltage; 24 VDC output voltage; 10 A output current; 0.06 ... 7.2 s buffer time; communication capability; 2,50 mm²

<https://www.wago.com/787-880>



Features:

- Capacitive buffer module bridges short duration voltage drops or load fluctuations
- For an uninterruptible power supply
- Internal diode between input and output enables operation with a decoupled output
- Buffer modules can be readily parallel-connected to increase buffer time or load current
- Potential-free contact for charge condition monitoring

Technical data

Input	
Nominal input voltage $U_{i\text{ nom}}$	24 VDC
Input voltage range	20 ... 30 VDC
Nominal mains frequency range	0 Hz
Input current I_i	$\leq 0.06\text{ A}$ (no load); $\leq 1\text{ A}$ (charging); $\leq 11\text{ A}$

Output	
Nominal output voltage $U_{o\text{ nom}}$	24 VDC
Output voltage range	$U_i - 0.5\text{ VDC}$ (rated operation); 20.4 ... 24 VDC (buffer mode)
Nominal output current $I_{o\text{ nom}}$	10 A
Current limitation	$1.1 \times I_{o\text{ nom}}$ (typ.)

Energy storage systems	
Buffer time	0.06 ... 7.2 s depends on load current and switch-on threshold
Switch-on threshold	DC 20 ... 24 V (adjustable)
Memory type	Supercaps
Charging time (typ.)	5 min

Signaling and Communication	
Signaling	1 x DC OK LED (green) 1 x Charge LED (yellow) 1 x DC not OK LED (red) 1 x Isolated relay contact (max. 30 VDC; 1 A)
Operation status indicator	Green LED ($U_o > 20\text{ V}$) Yellow LED (charging) Red LED ($U_o < 20\text{ V}$)

Efficiency/Power Losses	
Power loss P_i	$\leq 1.5\text{ W}$; $\leq 6.5\text{ W}$ (nominal load)



Safety and protection	
Isolation voltage (connectors – housing)	0.5 kVDC
Protection class	III
Protection type	IP20; per EN 60529
Reverse voltage protection	Yes
Resistance to reverse feed	≤ 35 VDC
Pollution degree	2
Parallel operation	Yes
Series operation	No
MTBF	typ. 87,600 h (at 25 °C); typ. 30,500 h (at 40 °C)

Connection Data	
Connection 1	
Connection type	Input/output/relay
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 231 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data	
Width	57 mm / 2.244 inches
Height	163 mm / 6.417 inches
Depth from upper-edge of DIN-rail	179 mm / 7.047 inches
Note (dimensions)	Height with connector

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Weight	1000 g

Environmental requirements	
Ambient temperature (operation)	-10 ... +50 °C
Ambient temperature (storage)	-10 ... +60 °C
Relative humidity	5 ... 96 % (no condensation permissible)

Standards and Specifications	
Conformity marking	CE
Standards/specifications	EN 60950 UL 508 EN 61000-6-2 EN 61000-6-3



Commercial data	
Product Group	6 (INTERFACE ELECTRONIC)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454909833
Customs tariff number	85049017000

Product Classification	
UNSPSC	39121006
eCl@ss 10.0	27-04-07-01
eCl@ss 9.0	27-04-07-01
ETIM 9.0	EC002540
ETIM 10.0	EC002540
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UL Underwriters Laboratories Inc.	UL 508	E255817			

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 787-880	

Documentation							
Bid Text				Instruction Leaflet			
787-880	12.07.2019	docx 21.33 KB		EPSITRON Capacitive Buffer Modules	pdf 516.78 KB		
787-880	12.07.2019	xml 6.18 KB					



CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 787-880	EPLAN Data Portal 787-880
	WSCAD Universe 787-880
	ZUKEN Portal 787-880

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white



Item No.: 210-831
Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white



Item No.: 210-832
Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

1.1.2 Mounting adapter

1.1.2.1 DIN-rail adapter



Item No.: 787-897
Carrier rail adapter made of zinc die-cast; for mounting 787-8xx devices to a DIN 35 rail; gray



Item No.: 787-896
Carrier rail adapter; for mounting 787-8xx devices to a DIN 35 rail; gray

1.1.2.2 Wall-mount adapter



Item No.: 787-895
Mounting carrier; for screw fixing of 787-8xx devices on mounting plate or wall without DIN 35 rail; gray

1.1.3 Tool

1.1.3.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured