



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	JUL29/14	L.CHAN
B	UPDATED SHIELD WITH NOTCH	APR 12/17	L.CHAN



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:
 PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0, COLOR: BLACK

CONTACTS: PHOSPHOR BRONZE
 (FLAT) PLATING: 30 μ" [0.76 MICRONS]
 MIN. GOLD ON MATING SURFACES.
 50 μ" [1.27 MICRONS]
 MIN. NICKEL UNDERPLATE
 100 μ" [2.54 MICRONS]
 MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: STAINLESS STEEL WITH TIN DIPPED ON SOLDER TAILS.

RECOMMENDED SOLDERING TEMPERATURE:
 WAVE SOLDERING TEMPERATURE AT 260°C MAXIMUM
 FOR 5 SEC MAXIMUM.

AMPHENOL PART NUMBER: RJHSE-3380

UNLESS SPECIFIED OTHERWISE		DRAWN <i>AMY.Z</i>	DATE <i>JUL29/14</i>	Amphenol Canada Corp. www.amphenolcanada.com	
PRIMARY UNITS	INCH	CHECKED <i>L.CHAN</i>	DATE <i>JUL29/14</i>		
SECONDARY	MILLIMETER	M.E. APP'D		TITLE SINGLE-PORT HIGH SPEED MODULAR JACK, VERTICAL MOUNT, 8P8C, SHIELDED, WITHOUT LED's, - RoHS COMPLIANT	
REFERENCE IN PARENTHESES		DWG APPR.			
GENERAL TOLERANCES		ENG. REL. NO.		DWG. NO. P-RJHSE-3380	
1 DECIMAL PLACE ±0.025		REF.			
2 DECIMAL PLACES ±0.020		THIRD ANGLE PROJECTION		REV B	
3 DECIMAL PLACES ±0.015					
ANGULAR DEGREES ±1.0°				CODE ID NO. 03554 DWG SIZE: C SCALE: <i>N/A</i> SHEET 1 OF 1	