

1 & 2 Pole - Low profile (15.7 mm height)
41.31 - 1 Pole 12 A (3.5 mm pin pitch)
41.52 - 2 Pole 8 A (5 mm pin pitch)
41.61 - 1 Pole 16 A (5 mm pin pitch)


PCB mount

- direct or via PCB socket

35 mm rail mount

- via screw and screwless sockets

- AC and DC coils
- 8 mm, 6 kV (1.2/50 μ s) isolation, coil-contacts
- Cadmium Free contact materials
- Flux proof: RT II standard, (RT III option)



FOR UL RATINGS SEE:

"General technical information" page V

Contact specification

Contact configuration

Copper side view

Copper side view

Copper side view

Rated current/

Maximum peak current

A

Rated voltage/

Maximum switching voltage

V AC

Rated load AC1

VA

Rated load AC15 (230 V AC)

VA

Single phase motor rating (230 V AC)

kW

Breaking capacity DC1: 30/110/220 V

A

Minimum switching load

mW (V/mA)

Standard contact material

Coil specification

Nominal voltage (U_N)

V AC (50/60 Hz)

V DC

Rated power AC/DC

VA (50 Hz)/W

Operating range

AC

DC

Holding voltage

AC/DC

Must drop-out voltage

AC/DC

Technical data

Mechanical life AC/DC

cycles

Electrical life at rated load AC1

cycles

Operate/release time

ms

Insulation between coil and contacts (1.2/50 μ s)

kV

Dielectric strength between open contacts

V AC


Ambient temperature range

°C

Environmental protection

Approvals (according to type)

- 3.5 mm contact pin pitch
- 1 Pole 12 A
- PCB direct or via socket



1 CO (SPDT)

12/25

250/400

3000

600

0.5

12/0.3/0.12

300 (5/5)

AgNi

24 - 230

5 - 6 - 12 - 24 - 48 - 60 - 110

0.75/0.4

(0.8...1.1) U_N

(0.7...1.5) U_N

0.8/0.4 U_N

0.15/0.1 U_N

$10 \cdot 10^6 / 10 \cdot 10^6$

$60 \cdot 10^3$

8/6


6 (8 mm)

1000

-40...+70 (AC); +85 (DC)

RT II

- 5 mm contact pin pitch
- 2 Pole 8 A
- PCB direct or via socket



2 CO (DPDT)

8/15

250/400

2000

400

0.3

8/0.3/0.12

300 (5/5)

AgNi

24 - 230

5 - 6 - 12 - 24 - 48 - 60 - 110

0.75/0.4

(0.8...1.1) U_N

(0.7...1.5) U_N

0.8/0.4 U_N

0.15/0.1 U_N

$10 \cdot 10^6 / 10 \cdot 10^6$

$60 \cdot 10^3$

8/6


6 (8 mm)

1000

-40...+70 (AC); +85 (DC)

RT II

- 5 mm contact pin pitch
- 1 Pole 16 A
- PCB direct or via socket



1 CO (SPDT)

16/30

250/400

4000

750

0.5

16/0.3/0.12

300 (5/5)

AgNi

24 - 230

5 - 6 - 12 - 24 - 48 - 60 - 110

0.75/0.4

(0.8...1.1) U_N

(0.7...1.5) U_N

0.8/0.4 U_N

0.15/0.1 U_N

$10 \cdot 10^6 / 10 \cdot 10^6$

$50 \cdot 10^3$

8/6

6 (8 mm)


1000

-40...+70 (AC); +85 (DC)


RT II

**1 & 2 Pole - Polarized bistable, Low profile
(15.7 mm height)****41.52 - 2 Pole 8 A (5 mm pin pitch)****41.61 - 1 Pole 16 A (5 mm pin pitch)****Printed Circuit mount**

- Polarized bistable relay with 2 coils
- 10 mm, 6 kV (1.2/50 μ s) isolation, coil-contacts
- Cadmium Free contact materials
- Flux proof: RT II standard

**41.52.6.xxx**


- 2 Pole, 8 A
- PCB direct mount



2 coil version:

A3(+) A2 (-) = Set


A3(+) A1 (-) = Reset



Copper side view

41.61.6.xxx


- 1 Pole, 16 A
- PCB direct mount



2 coil version:

A3(+) A2 (-) = Set

A3(+) A1 (-) = Reset



Copper side view

Contact specification

Contact configuration		2 CO (DPDT)	1 CO (SPDT)
Rated current/ Maximum peak current (I_N/I_{max})	A	8/15	16/30
Rated voltage/ Maximum switching voltage (U_N/U_{max})	V AC	250/400	250/400
Rated load AC1	VA	2000	4000
Rated load AC15 (230 V AC)	VA	350	750
Single phase motor rating (230 V AC)	kW	0.37	0.55
Breaking capacity DC1: 30/110/220 V	A	8/0.3/0.12	16/0.3/0.12
Minimum switching load	mW (V/mA)	500 (5/100)	500 (5/100)
Standard contact material		AgSnO ₂	AgSnO ₂

Coil specification

Nominal voltage (U_N)	V DC	5 - 12 - 24	5 - 12 - 24
Rated power (P_N)	W	0.65	0.65
Operating range	DC	(0.7...1.1) U_N	(0.7...1.1) U_N
Min. impulse duration	ms	20	20
Max. impulse duration	s	30	30

Technical data

Mechanical life DC	cycles	$5 \cdot 10^6$	$5 \cdot 10^6$
Electrical life at rated load AC1	cycles	$30 \cdot 10^3$	$30 \cdot 10^3$
Operate/release time	ms	10/5	10/10
Insulation between coil and contacts (1.2/50 μ s)	kV	6 (10 mm)	6 (10 mm)
Dielectric strength between open contacts	V AC	1000	1000
Ambient temperature range	°C	-40...+85	-40...+85
Environmental protection		RT II	RT II

Approvals (according to type)

—


Solid State Relays

Printed circuit mount:

- direct or via PCB socket

35 mm rail mount:



- via screw or screwless sockets
- Single circuit output switching options
 - 5 A 24 V DC
 - 3 A 240 V AC
- Silent, high speed switching with long electrical life
- LED indicator
- Low profile (15.7 mm)
- Wash tight: RT III
- 2500 V AC insulation, input-output



41.81 - 9024



- 5 A, 24 V DC output switching
- PCB or 93 Series sockets





Copper side view

41.81 - 8240



- 3 A, 240 V AC output switching
- Zero crossing switching
- PCB or 93 Series sockets



Copper side view

Output circuit

Contact configuration		1 NO (SPST-NO)	1 NO (SPST-NO)
Rated current/ Maximum peak current (10 ms)	A	5/40	3/40
Rated voltage/ Maximum blocking voltage	V	(24/35)DC	(240/—)AC
Switching voltage range	V	(1.5...24)DC	(12...275)AC
Repetitive peak off-state voltage	V _{pk}	—	600
Minimum switching current	mA	1	50
Max. "OFF-state" leakage current	mA	0.01	1
Max. "ON-state" voltage drop	V	0.3	1.1

Input circuit

Nominal voltage	V DC	12	24	12	24
Operating range	V DC	8...17	14...32	8...17	14...32
Control current	mA	5.5	9	8.8	9
Release voltage	V DC	4	9	4	9
Impedance	Ω	1550	2600	1030	2600

Technical data

Operate/release time	ms	0.05/0.25	10/10
Dielectric strength between input/output	V AC	2500	2500
Ambient temperature range	°C	-20...+60	-20...+60
Environmental protection		RT III	RT III

Approvals (according to type)



Ordering information

Electromechanical relay (EMR)

Example: 41 series low-profile PCB relay, 2 CO (DPDT), 24 V DC coil.

A

41.529.024.0010

Series — 41

Type — 5
3 = PCB - 3.5 mm pinning
5 = PCB - 5 mm pinning
6 = PCB - 5 mm pinning

No. of poles — 2
1 = 1 pole for
41.31, 12 A
41.61, 16 A
2 = 2 pole for
41.52, 8 A

Coil version — 9
6 = DC bistable, 2 coils
8 = AC
9 = DC

Coil voltage — 24
See coil specifications

A: Contact material
0 = Standard AgNi
4 = AgSnO₂
5 = AgNi + Au

B: Contact circuit
0 = CO (nPDT)
3 = NO (nPST)

D: Special versions
0 = Flux proof (RT II)
1 = Wash tight (RT III)
6 = Bistable version (RT II)

C: Options
0 = Production line 0
1 = Production line 1

Selecting features and options: only combinations in the same row are possible.

Preferred selections for best availability are shown in **bold**.

Type	Coil version	A	B	C	D
41.31	DC	0 - 4 - 5	0 - 3	1	0 - 1
41.52	DC	0 - 5	0 - 3	1	0 - 1
41.61	DC	0 - 4	0 - 3	1	0 - 1
41.31/52/61	AC	0	0	0	0
41.52	DC bistable	4	0	1	6
41.61	DC bistable	4	0 - 3	1	6

Solid state relay (SSR)

Example: 41 series SSR relay, 5 A output, 24 V DC supply.

41.817.024.9024

Series — 41

Type — 8
8 = SSR type

Output — 1
1 = 1 NO (SPST-NO)

Input circuit — 9024
See coil specifications

Output circuit
9024 = 5 A - 24 V DC
8240 = 3 A - 240 V AC

Electromechanical relay


Technical data

Insulation according to EN 61810-1							
		1 pole		1 pole bistable	2 pole		2 pole bistable
Nominal voltage of supply system	V AC	230/400		230/400	230/400		230/400
Rated insulation voltage	V AC	250	400	250	250	400	250
Pollution degree		3	2	2	3	2	2
Insulation between coil and contact set							
Type of insulation		Reinforced (8 mm)		Reinforced (10 mm)	Reinforced (8 mm)		Reinforced (10 mm)
Overvoltage category		III		III	III		III
Rated impulse voltage	kV (1.2/50 µs)	6		6	6		6
Dielectric strength	V AC	4000		4000	4000		4000
Insulation between adjacent contacts							
Type of insulation		—		—	Basic		Basic
Overvoltage category		—		—	III		III
Rated impulse voltage	kV (1.2/50 µs)	—		—	4		4
Dielectric strength	V AC	—		—	2000		2000
Insulation between open contacts							
Type of disconnection		Micro-disconnection			Micro-disconnection		
Dielectric strength	V AC/kV (1.2/50 µs)	1000/1.5			1000/1.5		
Conducted disturbance immunity							
Burst (5...50)ns, 5 kHz, on A1 - A2		EN 61000-4-4			level 4 (4 kV)		
Surge (1.2/50 µs) on A1 - A2 (differential mode)		EN 61000-4-5			level 3 (2 kV)		
Other data							
Bounce time: NO/NC	ms	4/6 (monostable) - 2/10 (bistable)					
Vibration resistance (5...55)Hz: NO/NC	g	15/2 (monostable) - 5/3 (bistable)					
Shock resistance	g	16 (monostable) - 10 (bistable)					
Power lost to the environment	without contact current	W	0.4 (monostable)				
	with rated current	W	1.7 (41.31)		1.2 (41.52)		1.8 (41.61)
Recommended distance between relays mounted on PCB	mm	≥ 5					

Contact specification


F 41 - Electrical life (AC) v contact current (monostable)

Types 41.31/61




F 41 - Electrical life (AC) v contact current (monostable)


Type 41.52



F 41 - Electrical life (AC) v contact current (bistable)




H 41- Maximum DC1 breaking capacity




- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of $\geq 100 \cdot 10^3$ can be expected.
 - In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.
- Note: the release time for the load will be increased.

R 41 - AC coil operating range v ambient temperature



- 1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.

R 41 - DC coil operating range v ambient temperature



- 1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.

Coil specifications

AC coil data

Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N
V		V	V	Ω	mA
24	8.024	19.2	26.4	350	31.6
230	8.230	184	253	32500	3.2

DC coil data

Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N
V		V	V	Ω	mA
5	9.005	3.5	7.5	62	80
6	9.006	4.2	9	90	66.7
12	9.012	8.4	18	360	33.3
24	9.024	16.8	36	1440	16.7
48	9.048	33.6	72	5760	8.3
60	9.060	42	90	9000	6.6
110	9.110	77	165	24200	4.5

DC coil data (bistable)

Nominal voltage	Coil code	Operating range			Resistance	Rated coil power
U_N		Set U_{min}	Reset U_{min}	Set/Reset U_{max}	R	I at U_N
V		V	V	V	Ω	mW
5	6.005	3.5	3.5	5.5	38	650
12	6.012	8.4	8.4	13.2	220	650
24	6.024	16.8	16.8	26.4	885	650

Solid state relay

A

Technical data

Other data			41.81 - 9024	41.81 - 8240
Power lost to the environment	without current	W	0.25	0.25
	with maximum current	W	1.75	3.5

Input specification


Input data - DC types

Nominal voltage U_N	Input code	Operating range		Release voltage	Impedance	Control current I at U_N
V		U_{min} V	U_{max} V	V	Ω	mA
12	7.012	8	17	4	1550	5.5
24	7.024	14	32	9	2600	9

Output specification


L 41 - Output current v ambient temperature

SSR - 5 A DC output types



L 41 - Output current v ambient temperature

SSR - 3 A AC output types



A




93.02

Approvals
(according to type):

**Screw terminal socket 35 mm (EN 60715) mounting**



Supply voltage	Relay type	Socket type	
6 V AC/DC	41.52.9.005.0010 or 41.61.9.005.0010	93.02.0.024	
12 V AC/DC	41.52.9.012.0010 or 41.61.9.012.0010	93.02.0.024	
24 V AC/DC	41.52/61.9.024.0010 or 41.81.7.024.xxxx	93.02.0.024	
60 V AC/DC	41.52.9.060.0010 or 41.61.9.060.0010	93.02.0.060	
(110...125)V AC/DC	41.52.9.110.0010 or 41.61.9.110.0010	93.02.0.125	
(220...240)V AC/DC	41.52.9.110.0010 or 41.61.9.110.0010	93.02.0.240	
(230...240)V AC	41.52.9.110.0010 or 41.61.9.110.0010	93.02.8.230	
6 V DC	41.52.9.005.0010 or 41.61.9.005.0010	93.02.7.024	
12 V DC	41.52/61.9.012.0010 or 41.81.7.012.xxxx	93.02.7.024	
24 V DC	41.52/61.9.024.0010 or 41.81.7.024.xxxx	93.02.7.024	
48 V DC	41.52.9.048.0010 or 41.61.9.048.0010	93.02.7.060	
60 V DC	41.52.9.060.0010 or 41.61.9.060.0010	93.02.7.060	
Accessories			
8-way jumper link	093.08 (see specification next page)		
Plastic separator	093.01 (see specification next page)		
Sheet of marker tags, 72 tags	060.72 (see specification next page)		
Technical data			
Rated values	10 A - 250 V		
Dielectric strength	6 kV (1.2/50 μs) between coil and contacts		
Protection category	IP 20		
Ambient temperature (U _N ≤ 60 V / > 60 V)	°C	−40...+70/−40...+55	
 Screw torque	Nm	0.5	
Wire strip length	mm	8	
Max. wire size for 93.02 socket	solid wire	stranded wire	
	mm ²	1 x 6 / 2 x 2.5	1 x 4 / 2 x 2.5
	AWG	1 x 10 / 2 x 14	1 x 12 / 2 x 14



Note: Not for bistable relays



Approvals
(according to type):



Screw terminal socket 35 mm (EN 60715) mounting


Supply voltage	Relay type	Socket type
6 V AC/DC	41.52.9.005.0010 or 41.61.9.005.0010	93.52.0.024
12 V AC/DC	41.52.9.012.0010 or 41.61.9.012.0010	93.52.0.024
24 V AC/DC	41.52/61.9.024.0010 or 41.81.7.024.xxxx	93.52.0.024
60 V AC/DC	41.52.9.060.0010 or 41.61.9.060.0010	93.52.0.060
(110...125)V AC/DC	41.52.9.110.0010 or 41.61.9.110.0010	93.52.0.125
(220...240)V AC/DC	41.52.9.110.0010 or 41.61.9.110.0010	93.52.0.240
(230...240)V AC	41.52.9.110.0010 or 41.61.9.110.0010	93.52.8.230
6 V DC	41.52.9.005.0010 or 41.61.9.005.0010	93.52.7.024
12 V DC	41.52/61.9.012.0010 or 41.81.7.012.xxxx	93.52.7.024
24 V DC	41.52/61.9.024.0010 or 41.81.7.024.xxxx	93.52.7.024
48 V DC	41.52.9.048.0010 or 41.61.9.048.0010	93.52.7.060
60 V DC	41.52.9.060.0010 or 41.61.9.060.0010	93.52.7.060

Accessories

8-way jumper link	093.08 (see table below)
Plastic separator	093.01 (see table below)
Sheet of marker tags, 72 tags	060.72 (see table below)

Technical data

Rated values	10 A - 250 V	
Dielectric strength	6 kV (1.2/50 µs) between coil and contacts	
Protection category	IP 20	
Ambient temperature (U _N ≤ 60 V / > 60 V)	°C	-40...+70/-40...+55
Wire strip length	mm	8
Max. wire size for 93.52 socket	solid wire	stranded wire
	mm ²	1 x 2.5
	AWG	1 x 14



Note: Not for bistable relays


Accessories



Approvals
(according to type):



8-way jumper link for 93.02 and 93.52 sockets	093.08 (blue)	093.08.0 (black)	093.08.1 (red)
Rated values	10 A - 250 V		



Plastic separator for 93.02 and 93.52 sockets	093.01
Thickness 2 mm, required at the start and the end of a group of interfaces. Can be used for visual separation group, must be used for: - protective separation of different voltages of neighbouring PLC interfaces according to VDE 0106-101 - protection of cut jumper links	



Sheet of marker tags for 38 x 2, plastic, 72 tags, 6 x 12 mm	060.72
---	--------

A



95.13.2



95.15.2


Approvals
(according to type):




PCB socket	95.13.2 (blue)	95.13.20 (black)	95.15.2 (blue)	95.15.20 (black)
For relay type	41.31		41.52, 41.61, 41.81 ⁽¹⁾	
Accessories				
Plastic retaining clip	095.42			
Technical data				
Rated values	10 A - 250 V*			
Dielectric strength	6 kV (1.2/50 μs) between coil and contacts			
Protection category	IP 20			
Ambient temperature	°C	−40...+70		

* For currents > 10 A, contact terminals must be connected in parallel (21 with 11, 24 with 14, 22 with 12).


⁽¹⁾ With the relay 41.81 the NO change-over contact will be 11-14.




41.31




41.52



41.81 - 9024




41.81 - 8240




95.13.2

Copper side view



41.61



95.15.2

Copper side view

Note: Not for bistable relays

Packaging codes

How to code and identify retaining clip and packaging options for sockets.

Example:

9 5 . 1 3 . 2 S L A

A Standard packaging

SL Plastic retaining clip

9 5 . 1 3 . 2

Without retaining clip