

SERIES 800 UN THREAD MATING Mighty Mouse Connectors and Cables

Right-Angle Jam-Nut Receptacle with PC Tails




Printed Circuit Board Right Angle I/O Header features gold-plated size #23 contacts. UN mating thread, and aluminum or stainless steel shells. Rubber seal protects mated connectors from water ingress. 5 amp current rating, 500 VAC voltage rating. Contacts are factory-installed and are non-removable. Thermoplastic rear housing has #2-56 threaded inserts for attaching to circuit board with customer-supplied mounting screws. Connectors attach to chassis or panel with low-profile jam-nut and O-ring. Available in six contact arrangements, these right angle headers are ideal for hostile environments where 100/1000BASE-T Ethernet RJ-45 commercial-grade jacks are not advised.

How To Order						
Sample Part Number		800-032	-07	M	7-10	P Z
Series	800-032 PCB Receptacle					
Shell Style	-07 = Jam-Nut					
Shell Material and Finish	C = Aluminum / Black Anodize (Non-Conductive) M = Aluminum / Electroless Nickel NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate MT = Aluminum / Nickel-PTFE Z1 = Stainless Steel / Passivated					
Shell Size - Insert Arrangement	5-3, 6-1, 6-4, 6-6, 6-7, 7-1, 7-10, 8-2, 8-13, 9-4, 9-19, 9-200, 10-2, 10-5, 10-201					
Contact Type	P = Pin, PC Tail S = Socket, PC Tail					
Shell Key Position (See Table I)	N = Normal X = Pos. X Y = Pos. Y Z = Pos. Z					

Table II: Shell Key Positions (See Note 1 and 2)	
Shell Size 5 & 6	Shell Size 7, 9 and 10
Key Position	Key Rotation
N Normal	150°
X	140°
Y	130°
Z	120°

NOTES

- Shell sizes 5 thru 6: master key is located at top dead center (TDC) for normal (N) position.
- Shell size 7 thru 12: master key is rotated 90° from TDC for normal position
- Material / finish:
 - Receptacle shell, jam-nut: aluminum alloy or CRES / see How to Order Table
 - Insulator: High Grade Rigid Dielectric / N.A.
 - Interfacial seal, O-ring: fluorosilicone
 - Contact: copper alloy / gold plate per ASTM B 488, Type II, Class 1.25, over a suitable underplate
 - Potting: epoxy




SERIES 800 UN THREAD MATING

Mighty Mouse Connectors and Cables

Right-Angle Jam-Nut Receptacle with PC Tails



RIGHT-ANGLE JAM-NUT MOUNT PCB RECEPTACLE - SHELL STYLE 07



Dimensions											
Size - Arr	A Flat ±.005 (±0.13)	B Flat	Ø C	D Threads	E	F	G ±.035 (±0.89)	H ±.005 (±0.13)	J	K	L
5-3	.282 (7.16) .291 (7.39)	.497 (12.62)	.538 (13.67)	.3125-28 UN-2A	.260 (6.60)	.235 (5.97)	.257 (6.53)	.050 (1.27)	.165 (4.19)	.310 (7.87)	.49 (12.45)
6-1	.350 (8.89) .359 (9.12)	.559 (14.20)	.602 (15.29)	.3750-28 UN-2A	.350 (8.89)	.225 (5.72)	.285 (7.24)	.050 (1.27)	.224 (5.69)	.385 (9.78)	.58 (14.73)
6-4		.559 (14.20)	.602 (15.29)	.3750-28 UN-2A	.330 (8.38)	.225 (5.72)	.285 (7.24)	.050 (1.27)	.224 (5.69)	.385 (9.78)	.58 (14.73)
6-6,6-7		.559 (14.20)	.602 (15.29)	.3750-28 UN-2A	.350 (8.89)	.225 (5.72)	.285 (7.24)	.050 (1.27)	.187 (4.75)	.408 (10.36)	.58 (14.73)
7-1	.409 (10.39)	.643 (16.33)	.664 (16.87)	.4375-28 UNEF-2A	.350 (8.89)	.296 (7.52)	.200 (5.08)	.092 (2.34)	.170 (4.32)	.452 (11.48)	.71 (18.03)
7-10	.418 (10.62)	.643 (16.33)	.664 (16.87)	.4375-28 UNEF-2A	.350 (8.89)	.296 (7.52)	.274 (6.96)	.092 (2.34)	.170 (4.32)	.452 (11.48)	.71 (18.03)
8-2	.471 (11.96)	.731 (18.57)	.770 (19.56)	.5000-28 UN-2A	.490 (12.45)	.320 (8.13)	.336 (8.53)	.092 (2.34)	.230 (5.84)	.490 (12.45)	.71 (18.03)
8-13	.480 (12.19)	.731 (18.57)	.770 (19.56)	.5000-32 UN-2A	.490 (12.45)	.320 (8.13)	.315 (8.00)	.092 (2.34)	.230 (5.84)	.490 (12.45)	.71 (18.03)
9-4	.528 (13.41) .537 (13.64)	.803 (20.40)	.872 (22.15)	.5625-28 UN-2A	.490 (12.45)	.362 (9.19)	.288 (7.32)	.092 (2.34)	.342 (8.69)	.600 (15.24)	.80 (20.32)
9-19		.803 (20.40)	.872 (22.15)	.5625-32 UN-2A	.490 (12.45)	.362 (9.19)	.283 (7.19)	.092 (2.34)	.342 (8.69)	.600 (15.24)	.80 (20.32)
9-200		.803 (20.40)	.872 (22.15)	.5625-28 UN-2A	.490 (12.45)	.362 (9.19)	.240 (6.10)	.092 (2.34)	.342 (8.69)	.600 (15.24)	.80 (20.32)
10-2	.602 (15.29) .611 (15.52)	.940 (23.88)	.976 (24.79)	.6250-28 UN-2A	.570 (14.48)	.397 (10.08)	.272 (6.91)	.092 (2.34)	.362 (9.19)	.640 (16.26)	.84 (21.34)
10-5		.940 (23.88)	.976 (24.79)	.6250-28 UN-2A	.570 (14.48)	.397 (10.08)	.305 (7.75)	.092 (2.34)	.362 (9.19)	.640 (16.26)	.84 (21.34)
10-201		.940 (23.88)	.976 (24.79)	.6250-28 UN-2A	.570 (14.48)	.397 (10.08)	.272 (6.91)	.092 (2.34)	.362 (9.19)	.640 (16.26)	.84 (21.34)





SERIES 800 UN THREAD MATING Mighty Mouse Connectors and Cables






Right-Angle Jam-Nut Receptacle with PC Tails




Panel Cutouts for Right Angle PCB Headers

Panel Cutouts for Right Angle PCB Headers				
 RECOMMENDED PANEL CUTOUTS EXCEPT 8-13	 RECOMMENDED PANEL CUTOUT FOR 8-13	Shell Size	A Flat +.004 +.000	øB ±.005
		5	.292 (7.42)	.322 (8.18)
		6	.358 (9.09)	.385 (9.78)
		7-1	.417 (10.59)	.447 (11.35)
		7-10	.417 (10.59)	.479 (12.17)
		8	.479 (12.17)	.510 (12.95)
		9	.536 (13.61)	.572 (14.53)
		10	.610 (15.49)	.635 (16.13)

SAMPLE KEYWAY POSITIONS FOR RIGHT ANGLE PCB HEADERS



SERIES 800 UN THREAD MATING




SERIES 800 UN THREAD MATING Mighty Mouse Connectors and Cables

Right-Angle Jam-Nut Receptacle PCB Footprints




RIGHT ANGLE PCB FOOTPRINTS: SOCKET CONNECTORS SHOWN


Patterns shown are for component mounting side of PCB. Contacts are .022 (0.56) max. diameter, mounting holes are 2-56 threaded inserts




5-3




6-1




6-4




6-6




6-7




7-1




7-10



8-2




8-13




Right-Angle Jam-Nut Receptacle PCB Footprints

RIGHT ANGLE PCB FOOTPRINTS: SOCKET CONNECTORS SHOWN


Patterns shown are for component mounting side of PCB. Contacts are .022 (0.56) max. diameter, mounting holes are 2-56 threaded inserts




9-4




9-19




9-200



10-2



10-5



10-201