


Data Sheet | Item Number: 788-354




Relay module; Nominal input voltage: 24 VDC; 1 changeover contact; Limiting continuous current: 16 A; for lamp loads; Red status indicator; Module width: 15 mm; 2,50 mm²; gray




<https://www.wago.com/788-354>



Color: ■ gray



Load limit curve



Current-carrying capacity curve



Notes	
Safety Information	A separator plate (e.g., 209-191) must be used for voltages greater than 250 V between adjacent relay modules and for compliance with the reinforced insulation requirements.
Note	Reinforced insulation between coil and contacts To protect the relay coils and contacts, inductive loads must be dampened with an effective protection circuit.

Technical data	
Control circuit	Load circuit
Nominal input voltage U _N	24 VDC
Input voltage range	-15 ... +20 %
Nominal input current at U _N	19 mA
	Number of changeover/switchover contacts
	1
	Contact material (relay)
	AgSnO ₂
	Limiting continuous current
	16 A
	Inrush current (resistive) max.
	(AC) 120 A / 0.05 s
	Switching Voltage, Max.
	250 VAC
	Switching power (resistive) max.
	AC 4000 VA; DC (see load limit curve)
	Recommended minimum load
	5 V / 100 mA
	Pull-in time (typ.)
	15 ms
	Drop-out time (typ.)
	5 ms
	Electrical life (NO; resistive load; 23 °C)
	100 x 10 ³ switching operations
	Mechanical life
	10 x 10 ⁶ switching operations

Signaling	
Status indicator	Red LED

Safety and protection	
Rated Voltage	250 V
Rated impulse withstand voltage	4 kV
Pollution degree	3
Dielectric strength (control/load circuit) (AC, 1 min)	5 kVrms
Dielectric strength (open contact) (AC, 1 min)	1 kVrms
Safety Information	A separator plate (e.g., 209-191) must be used for voltages greater than 250 V between adjacent relay modules and for compliance with the reinforced insulation requirements.
Protection type	IP20

Connection data	
Connection technology	Push-in CAGE CLAMP®
Solid conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Fine-stranded conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data	
Width	15 mm / 0.591 inches
Height	86 mm / 3.386 inches
Depth from upper-edge of DIN-rail	54 mm / 2.126 inches



Mechanical data		
Mounting type		DIN-35 rail

Material data		
Note (material data)		Information on material specifications can be found here
Color		gray
Fire load		0.92 MJ
Weight		44.1 g

Environmental requirements		
Ambient temperature (operation at U _N)		-40 ... +70 °C
Ambient temperature UL (operation at U _N)		-40 ... +50 °C
Ambient temperature (storage)		-40 ... +70 °C
Processing temperature		-25 ... +50 °C
Temperature range of connection cable		≥ (T _{ambient} + 20 K)

Standards and specifications		
Standards/specifications		EN 61010-2-201 EN 61810-1 EN 61373 UL 508 (max. 10 A)


Basic relay		
WAGO Basic Relay		788-195


Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		20 (1) pcs
Packaging type		Box
Country of origin		CN
GTIN		4055143184168
Customs tariff number		85364900990




Product classification		
UNSPSC		39122334
eCl@ss 10.0		27-37-16-01
eCl@ss 9.0		27-37-16-01
ETIM 9.0		EC001437
ETIM 8.0		EC001437
ECCN		NO US CLASSIFICATION








Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates		
General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03084
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 508	E175199 Vol.1 Sec.6

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 788-354	

Documentation				
Bid Text			Instruction Leaflet	
788-354	25.01.2019	docx 16.59 KB		
788-354	19.02.2019	xml 4.85 KB		
ausschreiben.de 788-354				

Documentation				
Instruction Leaflet				
Sockets with Elementary Relay/ SSR	V 1.0.1 09.10.2020	pdf 2271.22 KB		

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 788-354	EPLAN Data Portal 788-354
	
	WSCAD Universe 788-354
	
	ZUKEN Portal 788-354
	



1 Compatible Products

1.1 Optional Accessories

1.1.2 Ferrule

1.1.2.1 Ferrule



[Item No.: 216-241](#)
Ferrule; Sleeve for 0.5 mm² / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white



[Item No.: 216-242](#)
Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



[Item No.: 216-243](#)
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red



[Item No.: 216-244](#)
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black



[Item No.: 216-542](#)
Twin ferrule; Sleeve for 2 x 1 mm² / AWG 2 x 18; red, insulated; 12 mm long; red

1.1.3 Indicators

1.1.3.1 Status indication



[Item No.: 788-120](#)
Accessories for relay modules; Operation status indicator: red; Nominal operating voltage: 24 VDC

1.1.4 Jumper

1.1.4.1 Jumper



[Item No.: 788-118](#)
Jumper; for jumper slot; 2-way; from 1 to 3; insulated; light gray



[Item No.: 788-113](#)
Jumper; for jumper slot; 2-way; insulated; light gray



[Item No.: 859-402](#)
Jumper; for jumper slot; 2-way; insulated; light gray



[Item No.: 788-114](#)
Jumper; for jumper slot; 3-way; insulated; light gray



[Item No.: 788-115](#)
Jumper; for jumper slot; 4-way; insulated; light gray



[Item No.: 788-116](#)
Jumper; for jumper slot; 6-way; insulated; light gray



[Item No.: 788-117](#)
Jumper; for jumper slot; 8-way; insulated; light gray

1.1.5 Marking

1.1.5.1 Double marker carrier



[Item No.: 209-128](#)
Adaptor; gray



1.1.5.2 Group marker carrier



Item No.: 249-105
Group marker carrier; gray



Item No.: 209-145
Group marker carrier; white

1.1.5.3 Marker



Item No.: 209-183
Marker; white



Item No.: 793-502
WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-503
WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-504
WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-505
WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.5.4 Marking device



Item No.: 210-110
Fiber-tip pen

1.1.5.5 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

1.1.5.6 Protective marker cover



Item No.: 209-184
Protection cover; transparent

1.1.6 Tool


1.1.6.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured


Installation Notes

Conductor termination



Conductor termination

Commoning



Easy commoning using adjacent jumpers

Marking



Marking using WMB Multi markers and group marker carriers.