

## Communications/Signal PC Board Relays



- V23008, V23009/Power Relay 15 Series
- AC Actuating System
- Input Voltage = 42 VAC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 15 Amps.

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

- None Available

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

- Termination Type = Solder/Plug-In Terminals

- Actuating System = AC
- Input Voltage (VAC) = 42
- Contact Current Rating (Amps.) = 15
- Coil Resistance ( $\Omega$ ) = 76
- Coil Power, Nominal (VA) = 3.40 – 5.30
- Dielectric Between Coil and Contacts (V rms) = 2500

- Series = V23008, V23009/Power Relay 15
- Polarized = No

- Mounting Options = Socket
- Enclosure = Dust Protected
- [FCC Part 68 Isolation](#) = No
- Approved Standards = None
- Contact Material = Silver Nickel
- Approx. Dimensions (L x W x H) (mm [in]) = 53.00 x 46.50 x 61.00 [2.087 x 1.831 x 2.402]
- Compatible Socket = Without
- Contact Type = Single
- Pin Configuration = Industry Standard

- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Coil Magnetic System = Non Polarized, Monostable
- Coil Suppression Diode = Without

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

- Brand = Axicom