




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
CM	53					APVD
		A2	EOL		17JUL2020	ML SZ



- CONTACT: 0.00076 GOLD AT INTERFACE. 0.00254 MIN MATTE TIN ON SOLDER TAIL. 0.00127 MIN NICKEL UNDERPLATE ALL OVER.
- MATES WITH AMP-DUAC/PL PLUG RECEPTACLE 794152 AND ITS CONTACTS.
- CLEARANCE ENVELOPE FOR MATING PLUG RECEPTACLE LATCH.
- ALL POSTS STANDARD.
- CONTACT GROUND POST LOCATED IN CIRCUIT 3, ASSEMBLY P/N 5794172-3.
- NO POST IN POSITION 1
- NO POST IN POSITION 2
- NO POST IN POSITION 4



3-DIMENSIONAL MODEL NTS

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

6

6

6

6

5

9

8

7

BRASS

BRASS

BRASS

BRASS

BRASS

△

△

△

△

△

PBT, UL94V-0

PBT, UL94V-0

PBT, UL94V-0

PBT, UL94V-0

PBT, UL94V-0

NATURAL(WHITE)

NATURAL(WHITE)

NATURAL(WHITE)

NATURAL(WHITE)

NATURAL(WHITE)

5794172-6

5794172-5

5794172-4

5794172-3

5794172-2

5794172-3 SHOWN

MATERIAL

FINISH

MATERIAL

COLOR

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R. GRZYBOWSKI 04MAR05

CHK A. FRANTUM 04MAR05

APVD A. FRANTUM 04MAR05

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.2

2 PLC ± 0.13

3 PLC ± -

4 PLC ± -

ANGLES ± 8° 30'

PRODUCT SPEC 108-1646

APPLICATION SPEC 114-6067

WEIGHT -

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

HEADER ASSEMBLY, RIGHT ANGLE, 4 CIRCUIT, AMPDUAC/PL POWER CONNECTOR

A100779

5794172

1

1

REV A2

CUSTOMER DRAWING

SCALE 5:1

SHEET 1

OF 1

REV A2