Part Number : 1200688189
Product Description : M12 Signal, A-Coded, In-Line Splitter with Knurled Hexnuts, 1 x 4 Poles Male (Straight) to 2 x 3 Poles Female (90°), Black TPU WSOR Cable, 0.60m (1.97') Length
Series Number : 120009
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 884A31B30M006



Documents and Resources

Drawings

1200688189_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120009
Description	M12 Signal, A-Coded, In-Line Splitter with Knurled Hexnuts, 1 x 4 Poles Male (Straight) to 2 x 3 Poles Female (90°), Black TPU WSOR Cable, 0.60m (1.97') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Splitter - In-line
UPC	889056131049

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Black
Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	0.60m
Leg 2 Length	0.60m

Downloaded from Arrow.com.

Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Net Weight	87.003/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25° to +80°C

Downloaded from Arrow.com.