



## Catalog No. TY244MX

**Description:** CABLE TIE 29LB 14.5IN UV BLACK NYL

**UPC No** 5414363062097

**Home > Wire & Cable Management > Ty-Rap > Cable ties**

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 366mm (14.4 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1.15mm (0.045 Inch), Tensile Strength Rating of 130 Newtons (29 pounds), Bulk Pack

### Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

### Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	29 pounds , 130 newtons

### Classifications

Brand Name	Ty-Rap
Standard	UL E49405

### Dimensions

Width	0.14 in , 3.6 mm
Length	14.4 in , 366 mm
Thickness	0.04 in , 1.0 mm
Bundle Diameter	0.08 to 4.02 in , 2 to 102 mm

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000046 Cable tie
Band width	3.6 mm
Length belt/tape/tie	366 mm
Length belt/tape/tie	14.4 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	102 mm
Min. holding force	130 N
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

#### Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441406	N/A	1349334_2014-11-06	N/A
UL	E49405	N/A	ZODZ	N/A	N/A