

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-2.
TERMINALS: BRASS, BRIGHT TIN PLATE.
SCREWS: 6-32, STEEL, PLATED ZINC W/ CLEAR CHROMATE COATING. UNLESS OTHERWISE SPECIFIED.

ELECTRICAL:
MAXIMUM CURRENT: 20A.
OPERATING VOLTAGE: 300V.
WIRE RANGE: 12-22 AWG.




ENVIRONMENTAL:
OPERATING TEMP.: -60°C TO 105°C

- 1

WHITE MARKING AS SHOWN.
- 2

SCREWS BOTTOMED.
- 3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
—	—		A3	REVISED PER ECO-11-012226		15JUN11	HMR CR

3 OBSOLETE	7.561	7.125	20	RSB6VP201202	2-1437408-6
	7.186	6.750	19	RSB6VP191202	2-1437408-4
12	6.811	6.375	18	RSB6VP181202	2-1437408-1
	6.061	5.625	16	RSB6VP16120222N1760	2-1437417-5
12	6.061	5.625	16	RSB6VP16120222N60	1-1437408-9
12	6.061	5.625	16	RSB6VP16120221N2060	1-796609-6
12	6.061	5.625	16	RSB6VP1620221N60	1-1437408-7
3 OBSOLETE	6.061	5.625	16	RSB6VP161202	1-1437408-6
	5.311	4.875	14	RSB6VP141202	4-1437408-2
3 OBSOLETE	4.936	4.500	13	RSB6VP131202	4-1437408-0
	4.561	4.125	12	RSB6VP121202	1437408-8
3 OBSOLETE	4.186	3.750	11	RSB6VP111202	1437408-7
12	3.811	3.375	10	RSB6VP101202	1437408-1
	3.436	3.000	9	RSB6VP09120222N60	9-1437407-6
12	3.436	3.000	9	RSB6VP09120221N60	9-1437407-5
3 OBSOLETE	3.436	3.000	9	RSB6VP091202	9-1437407-4
	3.061	2.625	8	RSB6VP081202	8-1437407-8
3 OBSOLETE	2.686	2.250	7	RSB6VP071902	8-1437407-7
	2.686	2.250	7	RSB6VP071202	8-1437407-6
1	2.311	1.875	6	RSB6VP061202	7-1437407-9
	1.936	1.500	5	RSB6VP05120221AA	796933-1
3 OBSOLETE	1.936	1.500	5	RSB6VP051202	7-1437407-4
	1.561	1.125	4	RSB6VP041202	7-1437407-0
1	1.186	.750	3	RSB6VP03120211	1986391-3
1	1.186	.750	3	RSB6VP031202	6-1437407-3
	.811	.375	2	RSB6VP08120222N1960	5-1437407-9
2	.811	.375	2	RSB6VP021202N60	6-1437407-0
2	.811	.375	2	RSB6VP021202	5-1437407-8
	DIM B	DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

0

1

2

3

4

PLC

± -

± -

± .02

± .010

± -

ANGLES

± 2°

MATERIAL

-

FINISH

-

DWN S SCHLEGEL 02OCT2008

CHK S MACE 10/2/08

APVD S MACE 10/2/08

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

RSB6 ASSEMBLY

SIZE A3

CAGE CODE 00779

DRAWING NO C-5

RESTRICTED TO -

SCALE 1:1


SHEET 1 OF 2

REV A3


OBSOLETE

NOT the LATEST REVISION


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
—	—		—	SEE SHEET 1	—	—




5-1437407-9




1-796609-6




1986391-3




2-1437417-5




796933-1




9-1437407-5



9-1437407-6



1-1437408-9



1-1437408-7

3 OBSOLETE	9.061	8.625	24	RSB6VP241202	3-1437408-2
	8.686	8.250	23	RSB6VP231202	3-1437408-1
	8.311	7.875	22	RSB6VP221202	2-1437408-8
	7.936	7.500	21	RSB6VP211202	2-1437408-7
	DIM B	DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL	02OCT2008	TE Connectivity			
DIMENSIONS: INCHES		CHK S MACE	10/2/08	NAME RSB6 ASSEMBLY			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .02 3 PLC ± .010 4 PLC ± — ANGLES ± 2°	APVD S MACE	10/2/08				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL —	FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-5-1437407-8	RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 1:1	SHEET 2 OF 2	REV A3	