

Part Number : 1300100233
Product Description : Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow PVC Cable, 4.60m (15.09') Length
Series Number : 130010
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 113020A01F150

Documents and Resources

Drawings

1300100233_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow PVC Cable, 4.60m (15.09') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	N/A
Type	Double Ended
UPC	78678843778

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Physical

Cable Diameter	10.41mm (.410")
Cable Length	4.60m (15.09')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male

Downloaded from Arrow.com.

Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	131.000/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	STOOW
Wire Size (AWG)	16

Downloaded from Arrow.com.