

Bipolar Transistors Silicon PNP Epitaxial Type (PCT Process)(Bias Resistor built-in Transistor)

RN2421,RN2422,RN2423,RN2424,RN2425,
RN2426,RN2427


1. Applications

- Switching
- Inverter Circuits
- Interfacing
- Driver Circuits

2. Features

- (1) High collector current: $I_C = \sim 800\text{ mA (max)}$
- (2) The integrated bias resistor reduces the number of external parts required, making it possible to reduce system size and assembly time.
- (3) Toshiba offers transistors with a wide range of resistance to accommodate various circuit designs.
- (4) Complementary to RN1421 to RN1427
- (5) Low $V_{CE(sat)}$

3. Equivalent Circuit




4. Bias Resistor Values

Part No.	R1 (kΩ)	R2 (kΩ)
RN2421	1	1
RN2422	2.2	2.2
RN2423	4.7	4.7
RN2424	10	10
RN2425	0.47	10
RN2426	1	10
RN2427	2.2	10

Start of commercial production
1988-02

5. Packaging and Pin Assignment



6. Absolute Maximum Ratings (Note) (Unless otherwise specified, $T_a = 25\text{ }^{\circ}\text{C}$)

Characteristics	Part Number	Symbol	Rating	Unit
Collector-base voltage	RN2421 to RN2427	V_{CBO}	-50	V
Collector-emitter voltage		V_{CEO}	-50	V
Emitter-base voltage	RN2421 to RN2424	V_{EBO}	-10	V
	RN2425, RN2426		-5	
	RN2427		-6	
Collector current	RN2421 to RN2427	I_C	-800	mA
Collector power dissipation		P_C	200	mW
Junction temperature		T_j	150	$^{\circ}\text{C}$
Storage temperature		T_{stg}	-55 to 150	$^{\circ}\text{C}$

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

7. Electrical Characteristics (Unless otherwise specified, $T_a = 25^\circ\text{C}$)

Characteristics		Symbol	Test Condition	Min	Typ.	Max	Unit
Collector cut-off current	RN2421 to RN2427	I_{CBO}	$V_{CB} = -50\text{ V}, I_E = 0\text{ mA}$	—	—	-100	nA
		I_{CEO}	$V_{CE} = -50\text{ V}, I_B = 0\text{ mA}$	—	—	-500	nA
Emitter cut-off current	RN2421	I_{EBO}	$V_{EB} = -10\text{ V}, I_C = 0\text{ mA}$	-3.85	—	-7.14	mA
	RN2422			-1.75	—	-3.25	
	RN2423			-0.82	—	-1.52	
	RN2424			-0.38	—	-0.71	
	RN2425		$V_{EB} = -5\text{ V}, I_C = 0\text{ mA}$	-0.365	—	-0.682	
	RN2426			-0.35	—	-0.65	
	RN2427		$V_{EB} = -6\text{ V}, I_C = 0\text{ mA}$	-0.378	—	-0.703	
DC current gain	RN2421	h_{FE}	$V_{CE} = -1\text{ V}, I_C = -100\text{ mA}$	60	—	—	—
	RN2422			65	—	—	
	RN2423			70	—	—	
	RN2424			90	—	—	
	RN2425			90	—	—	
	RN2426			90	—	—	
	RN2427			90	—	—	
Collector-emitter saturation voltage	RN2421	$V_{CE(sat)}$	$I_C = -50\text{ mA}, I_B = -2\text{ mA}$	—	—	-0.25	V
	RN2422 to RN2427		$I_C = -50\text{ mA}, I_B = -1\text{ mA}$	—	—	—	
Input voltage (ON)	RN2421	$V_{I(ON)}$	$V_{CE} = -0.2\text{ V}, I_C = -100\text{ mA}$	-1.0	—	-3.5	V
	RN2422			-1.4	—	-4.5	
	RN2423			-2.0	—	-6.5	
	RN2424			-3.0	—	-12.0	
	RN2425			-0.6	—	-2.0	
	RN2426			-0.7	—	-2.5	
	RN2427			-1.0	—	-3.0	
Input voltage (OFF)	RN2421 to RN2424	$V_{I(OFF)}$	$V_{CE} = -5\text{ V}, I_C = -0.1\text{ mA}$	-0.8	—	-1.3	V
	RN2425, RN2426			-0.4	—	-0.8	
	RN2427			-0.5	—	-1.0	
Transition frequency	RN2421 to RN2427	f_T	$V_{CE} = -5\text{ V}, I_C = -20\text{ mA}$	—	200	—	MHz
Collector output capacitance	RN2421 to RN2427	C_{ob}	$V_{CB} = -10\text{ V}, I_E = 0\text{ mA}, f = 1\text{ MHz}$	—	13	—	pF
Input resistance	RN2421	R_1	—	0.7	1.0	1.3	k Ω
	RN2422			1.54	2.2	2.86	
	RN2423			3.29	4.7	6.11	
	RN2424			7	10	13	
	RN2425			0.329	0.47	0.61	
	RN2426			0.7	1.0	1.3	
	RN2427			1.54	2.2	2.86	
Resistor ratio	RN2421 to RN2424	$R1/R2$	—	0.9	1.0	1.1	—
	RN2425			0.0423	0.047	0.0517	
	RN2426			0.09	0.1	0.11	
	RN2427			0.2	0.22	0.24	

8. Marking




Fig. 8.1 Marking RN2421




Fig. 8.2 Marking RN2422




Fig. 8.3 Marking RN2423




Fig. 8.4 Marking RN2424




Fig. 8.5 Marking RN2425




Fig. 8.6 Marking RN2426




Fig. 8.7 Marking RN2427

9. Characteristics Curves (Note)




Fig. 9.1 RN2421 I_C - $V_{I(ON)}$




Fig. 9.2 RN2422 I_C - $V_{I(ON)}$




Fig. 9.3 RN2421 I_C - $V_{I(OFF)}$




Fig. 9.4 RN2422 I_C - $V_{I(OFF)}$




Fig. 9.5 RN2421 h_{FE} - I_C




Fig. 9.6 RN2422 h_{FE} - I_C




Fig. 9.7 RN2423 I_C - $V_{I(ON)}$




Fig. 9.8 RN2424 I_C - $V_{I(ON)}$




Fig. 9.9 RN2423 I_C - $V_{I(OFF)}$




Fig. 9.10 RN2424 I_C - $V_{I(OFF)}$




Fig. 9.11 RN2423 h_{FE} - I_C




Fig. 9.12 RN2424 h_{FE} - I_C




Fig. 9.13 RN2425 I_C - $V_{I(ON)}$




Fig. 9.14 RN2426 I_C - $V_{I(ON)}$




Fig. 9.15 RN2425 I_C - $V_{I(OFF)}$




Fig. 9.16 RN2426 I_C - $V_{I(OFF)}$




Fig. 9.17 RN2425 h_{FE} - I_C




Fig. 9.18 RN2426 h_{FE} - I_C




Fig. 9.19 RN2427 I_C - $V_{I(ON)}$




Fig. 9.20 RN2427 I_C - $V_{I(OFF)}$





Fig. 9.21 RN2427 h_{FE} - I_C

Note: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

Package Dimensions

Unit: mm



Weight: 12 mg (typ.)

Package Name(s)
Nickname: S-Mini

RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA".

Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications.
TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.

- **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").**

Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant.

IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.

For details, please contact your TOSHIBA sales representative or contact us via our website.

- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NON-INFRINGEMENT.**
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**