

## Technical data sheet

Article number:  
309-50643

TF24-6.4/3.2



<b>Product Group</b>	Heat shrinkable tubing 2:1 - flexible and transparent
<b>Product Family</b>	TF24
<b>Material</b>	Polyolefin, cross-linked (PO-X)
<b>Colour</b>	Transparent (CL)
<b>Behaviour at Heat Shock</b>	not dripping, not fluid, not cracking
<b>Behaviour At Low Temperature</b>	not cracking
<b>Dielectric Strength</b>	30 kV/mm
<b>Elongation at break (min.)</b>	450 %
<b>Elongation At Heat Aging</b>	250 %
<b>Heat Aging Test</b>	168h/175°C
<b>Heat Shock Test</b>	4h/250°C
<b>Longitudinal Change After Shrinkage</b>	+/-5% max.
<b>Min. Shrink Temperature - °C</b>	+110 °C
<b>Operating Temperature</b>	-55 °C to +135 °C
<b>Package Content</b>	60 m
<b>Package Content packed in</b>	reel
<b>Recov. Ø d max.</b>	3.2 mm
<b>Shrink Ratio</b>	2:1
<b>Specifications</b>	VG 95343-5:2016-10
<b>Supplied Ø D min.</b>	6.4 mm
<b>Tensile Strength</b>	20 MPa
<b>Wall (WT)</b>	0.64 mm
<b>Water Absorption</b>	0.2 %

