




HONEYWELL PART NUMBER
23SX26
PRODUCT CODE VDP0500
JG-NUMBER JG-83642

REV	DOCUMENT	CHANGED BY	CHECK
11	0087806	SBH 21MAR12	CMH



PLASTIC PLUNGER




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - MOVABLE CONTACT MATERIAL - GOLD PLATED, GOLD ALLOY
- 4 - STATIONARY CONTACT MATERIAL - GOLD ALLOY
- 5 - SWITCH WILL WITHSTAND TEMPERATURE OF 185°F

RELEASE NO.	PR-10247
REPLACES	

CHARACTERISTICS
OPERATING FORCE - - - 5 OZ MAX
RELEASE FORCE - - - - 1 OZ MIN
DIFFERENTIAL TRAVEL - - - .005 MAX
OVERTRAVEL - - - - - .004 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
30 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	0.5 AMP	0.5 AMP
RESISTIVE	1 AMP	1 AMP
MAXIMUM INRUSH 2 AMP		
APPROVALS	KEMA, CE	1A 250 V ~ T125 25E3 
	UL, CSA	1A 125 VAC   BRAND L22J

DESIGN UNITS: INCH		
TOLERANCES UNLESS NOTED:		
NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±
THIRD ANGLE PROJECTION		
		

DRAWN	SPK	21FEB08
CHECK	RJ	21FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell				
TITLE SWITCH - BASIC				
SIZE B	TYPE I	DRAWING NAME 23SX26		REV 11
SCALE -	WEIGHT: .003 LB MAX		SHEET 1 OF 1	