

Part Number : [765460003](#)

Product Description : 2.54mm, 3.00mm Pitch
EXTreme Ten60Power Vertical Plug Assembly, 20 Signal
Circuits, 10 Power Circuits

Series Number : 76546

Status : Active

Product Category : Board-to-Board Connectors

Documents and Resources

Drawings

[765460003_sd.pdf](#)

[PK-76546-002-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[AS-46436-100-001.pdf](#)

[PS-46436-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	76546
Description	2.54mm, 3.00mm Pitch EXTreme Ten60Power Vertical Plug Assembly, 20 Signal Circuits, 10 Power Circuits
Application	Board-to-Board
Comments	Short Power: P1P5, P10 Short Signal: S6-S10, S16-S20
Component Type	Plug
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	884982253766

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A, 60.0A
-------------------------------	-------------

Physical

Breakaway	No
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	Yes
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	33.530/g
Number of Rows	10, 2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.58mm
PC Tail Length	3.25mm
Pitch - Mating Interface	2.54mm, 3.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	10p - 20s
Termination Interface Style	Solder or Weld, Through Hole

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

This document was generated on May 04, 2026