

Conductor marker - UC-WMC 4,4 (15X5,5) - 0818182

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, CMS-P1-PLOTTER, PLOTMARK, Mounting type: clip on, Cable diameter: 2.8-4.4 mm, Lettering field: 15 mm x 5.5 mm

Why buy this product

- ✓ The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements

RoHS

Key Commercial Data

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 STK |
| Minimum order quantity | 8 STK |
| GTIN |  4 046356 133517 |
| GTIN | 4046356133517 |
| Weight per Piece (excluding packing) | 12.000 g |
| Custom tariff number | 39269097 |
| Country of origin | Poland |

Technical data

Dimensions

| | |
|----------------|-------------------|
| Width (a) | 15 mm |
| Cable diameter | 2.8 mm ... 4.4 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

General

| | |
|-------|-------|
| Color | white |
|-------|-------|

Conductor marker - UC-WMC 4,4 (15X5,5) - 0818182

Technical data

General

| | |
|---------------------------------------------------------------------|-------------------------------------|
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 15 |
| Number of individual labels per row | 3 |
| RoHS compliant | Yes |
| Printability | UV LED technology |
| | Plotter |
| Device | 5147999 BLUEMARK CLED |
| | 5144615 CMS-P1-PLOTTER |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result | Test passed |
| Marking mounting type | clip on |

Standards and Regulations

| | |
|----------------------------------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2 |