

COAXIAL ADAPTER, PC 1.85 - MMPX, 50 Ohm, plug / jack (male / female)

33_PC185-MMPX-50-2/199_NE

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
PC 1.85	plug (male)	IEC 60169-32
MMPX	jack (female)	HUBER+SUHNER MMPX STD (Patent US 7.294.023)

Interface and material data		
PC 1.85		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	SUCOPRO / Gold Plating
Outer conductor	Stainless steel	Passivated (Plating)
Body	Stainless steel	Passivated (Plating)
Insulator	LCP (Liquid crystal polymer)	
Coupling nut	Stainless steel	Passivated (Plating)
MMPX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer conductor	Copper Beryllium Alloy	SUCOPRO Plating
Body	Stainless steel	Passivated (Plating)
Insulator	LCP (Liquid crystal polymer)	

Electrical data	
Impedance	50 Ω
Interface frequency	67 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 67 GHz	20 dB	1.222

COAXIAL ADAPTER, PC 1.85 - MMPX, 50 Ohm, plug / jack (male / female)
33_PC185-MMPX-50-2/199_NE

Mechanical data			
Weight		0.005 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-55 °C ... 155 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84132750	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
Ordering Information Table			
Item number	Item description		Packaging type
84132750	33_PC185-MMPX-50-2/199_NE		Single
Additional Information			
Remarks		Electrical values: mated adaptor pair	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2184 / Date of publication: 12.07.2025 / uncontrolled copy