




Part Number : [330113004](#)

Product Description : MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Silver Plating, Grip Code M3, Left Reel Payoff, Contact Material Thickness 0.30mm, Preferred Terminal for use in Sealed Application with 0.35-0.50mm²

Series Number : 33011

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[330113004 sd.pdf](#)

[313025040-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-33000-001-001.pdf](#)

[AS-33000-001-FR-001.pdf](#)


[AS-33000-001-001.pdf](#)

[PS-33012-002-001.pdf](#)

[TS-33000-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Crimp Terminals
Series	33011
Description	MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Silver Plating, Grip Code M3, Left Reel Payoff, Contact Material Thickness 0.30mm, Preferred Terminal for use in Sealed Application with 0.35-0.50mm ²
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Comments	Left Reel Payoff
Product Name	MX150
UPC	884982250604

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Gender	Male
Grip Code	M3
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	0.300/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.70mm max.
Wire Size (AWG)	N/A
Wire Size mm ²	0.35-0.50

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Single Row Male Connector Assemblies	<u>33481</u>
MX150 Mat-Sealed Dual Row Male Connector Assemblies	<u>33482</u>

Application Tooling

Global

Description	Part Number
Extraction Toolkit for MX150 Connectors	<u>2002220700</u>
FA2 Mechanical Feed Crimp Applicator for MX150 Male Terminals, 0.35mm ² and 0.50mm ² ISO Wire	<u>638082400</u>
FA2 Pneumatic Feed Crimp Applicator for MX150 ISO (M3)	<u>638082410</u>

Male Terminals, 0.35mm ² and 0.50mm ² ISO wire	
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	<u>638131500</u>
Hand Crimp Tool for ISO (M3) Blade Terminals	<u>638233600</u>
FineAdjust Applicator for SRC Connector using MX150 (M3) Blade Terminals, 0.50mm ² wires	<u>639041300</u>

This document was generated on Apr 13, 2026