







PRODUCT NUMBER SEE SHEET 2




spec ref	*	dr	Eddy Zeng	2014/01/24	projection	MM	size	A3	scale	3:2
tolerance std	ASME Y14.5	eng	Rainbow Zhan	2015/09/28	chr	Fancy Zhang	2015/09/29	ecn no	ELX-DG-22054-1	
		appr	Pei-Ming Zheng	2015/09/29	product family	PwrBlade+	rel level	Released		
surface	✓	linear	0.X	±0.5	FCI	8HP + 60S	dwg no	10106125-8015001	rev	B
			0.XX	±0.25		RA PF HEADER				
			0.XXX	±0.10						
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.	Product - Customer Drw	sheet 1 of 3			



Copyright FCI.

PRODUCT NO.	ROW S		HIGH POWER								SIGNAL																
		E1	P1	P2	P3	P4	P5	P6	P7	P8	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	E2	
10106125-8015001LF	D C B A		<div>HE</div>	<div>HE</div>	<div>HE</div>	<div>HE</div>	<div>HE</div>	<div>HE</div>	<div>HE</div>	<div>HE</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	<div>SD</div>	



CODE	DESCRIPTION
HE	STD HIGH POWER CONTACT (3.05)
SA	STD SIGNAL CONTACT, ROW A (3.05)
SB	STD SIGNAL CONTACT, ROW B (3.05)
SC	STD SIGNAL CONTACT, ROW C (3.05)
SD	STD SIGNAL CONTACT, ROW D (3.05)

dr	Eddy Zeng	2014/01/24	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2			
eng	Rainbow Zhan	2015/09/28			ecn no	ELX-DG-22054-1					
chr	Fancy Zhang	2015/09/29			rel level	Released					
appr	Pei-Ming Zheng	2015/09/29	product family		PwrBlade+						
<div></div>			title			8HP + 60S		dwg no	10106125-8015001	rev	B
RA PF HEADER											
www.fci.com			cat. no.		Product - Customer Drw				sheet 2 of 3		

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



Copyright FCI.

dr	Eddy Zeng	2014/01/24	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2	
eng	Rainbow Zhan	2015/09/28			ecn no	ELX-DG-22054-1			
chr	Fancy Zhang	2015/09/29			rel level	Released			
appr	Pei-Ming Zheng	2015/09/29			product family	PwrBlade+			
<div>www.fci.com</div>			<div>8HP + 60S</div> <div>RA PF HEADER</div>			<div>dwg no</div> <div>10106125-8015001</div>	<div>rev</div> <div>B</div>	sheet 3 of 3	
cat. no.			Product - Customer Drw						