


# 3216LV

## Fast-acting Line-voltage Chip™ surface mount fuse

RoHS



### Product features

- Surface mount fuse, fast acting, 125 Vac
- Utilize thick and thin metal film technologies for superior fusing action and enhanced reliability.

### Agency information

- UL Recognition Guide & File numbers: JDYX2 & E19180.
- CSA Component Acceptance: 053787 C 000 & Class No: 1422 30

ELECTRICAL CHARACTERISTICS	
% of Amp Rating	Opening Time
100%	4 hours minimum
250%	5 seconds maximum


SPECIFICATIONS								
Part number	Current rating (A)	Voltage rating Vac/dc	Interrupting rating @ 125 Vac/dc (A)	Typical melting integral @ 10X rated current (A <sup>2</sup> sec)	AC	DC	Typical resistance @ ≤ 10% rated current (Ω)	Typical voltage drop @ rated current (V)
3216LV250-R	250 mA	125	50	0.00016	0.000084		3.5	1.4
3216LV375-R	375 mA	125	50	0.001	0.0002		1.75	0.73
3216LV500-R	500 mA	125	50	0.0014	0.0019		0.98	0.66
3216LV750-R	750 mA	125	50	0.0033	0.00950		0.54	0.63
3216LV1-R	1	125	50	0.020	0.0084		0.345	0.63
3216LV1.25-R	1.25	125	50	0.035	0.021		0.255	0.62
3216LV1.5-R	1.5	125	50	0.038	0.024		0.165	0.49

#### Notes:


1. AC interrupting rating (Measured at rated voltage with a unity power factor)
2. DC interrupting rating, (Measured at rated voltage, time constant of less than 50 microseconds, battery source)
3. Voltage drop measured at rated current after temperature stabilizes at 23 ± 3 °C
4. Typical melting  $I^2t$  (Measured with a battery bank at rated voltage and 50 A current, time constant of calibrated circuit less than 50 microseconds)
5. It is recommended that fuses be mounted with ceramic (white) side facing up
6. Device designed to carry rated current for four hours minimum. An operating current of 80% or less of rated current is recommended, with further derating required at elevated ambient temperatures

**Dimensions- mm (inches)**


Drawing not to scale



**Land pattern- mm (inches)**



**Time current curve**



<b>Packaging code</b>	
Packaging code	Description
TR-	3000 fuses on 8 mm tape-and-reel on a 7 inch (178 mm) reel per EIA Standard 481

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

**Eaton**  
**Electronics Division**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com/electronics

© 2020 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 2541  
August 2020

Eaton is a registered trademark.

All other trademarks are property  
of their respective owners.

Follow us on social media to get the  
latest product and support information.

