



**Part Number :** [1300068274](#)

**Product Description :** Mini-Change A-Size Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 16 AWG, Gray TPU Cable, 1.0m (3.28') Length

**Series Number :** 130006

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 105001B35M010



---

## Documents and Resources

### Drawings

[1300068274 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 10(a) per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 16 AWG, Gray TPU Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	193264204601

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	7.80mm (.307")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail

Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Electrophoretic Zinc Alloy
Material - Plating Mating	Gold
Net Weight	79.150/g
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	16

---

This document was generated on Dec 29, 2025