

EC No.

Battery Disconnecter 200A

Page 1 of 1

30
ø 7
38 ±0.5
ø 54
M8
19
109 ±1
ø 22
31.6 ±1
~63 (OFF)
35

Circuit

Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MΩm
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	to 32VDC
Duty Rating	200A
Overload	500A-180sec. 1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	4G / 50-2000Hz
Shock G-Level	6G / 11ms
Weight	~155g / 0.34 Pound
Temperature Range	-40°C to +85°C
Wire Section (at nominal Load)	min. 70mm ²
Switch Lever	removeable
Max. Torque (Main Contacts)	12-13Nm

Drawn	27.09.2018	Seeger	mm	Scale 1:1		Drawing No: 35-210-060-R
Check	22.10.2018	Grind				

General Tolerances
DIN ISO 2768 cL


NSN:

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	TE STANDARD	08MAY2024	KS	RB

NOTE
Bemerkungen:

1 TE-CONNECTIVITY ORDER-NUMBER
TE-connectivity Bestellnummer

2 DO NOT SWITCH UNDER LOAD!
Nicht unter Last schalten!



K1135221	1	A	BATTERY DISCONNECTOR 200A Batterietrennschalter 200A	1
TE ORDER-NO.	REV.		DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	DIN ISO 2768 cL
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH
MATERIAL	

DWN	K.Seeger	27SEP2018
CHK	K.Seeger	27SEP2018
APVD	U.Grindemann	22OCT2018
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT		
CUSTOMER DRAWING		



BATTERY DISCONNECTOR 200A
Batterietrennschalter 200A

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	35-210-060-R	-
SCALE	1:1	SHEET 1 OF 1	REV A