



Part Number : [1200945022](#)

Product Description : Brad M23 Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 22-18 AWG, PUR Cable, 10.0m (32.81') Length

Series Number : 120094

Status : Obsolete

Product Category : Circular Industrial Cordsets

Engineering Number : K02100P80M100



Documents & Resources

Drawings

[1200945022 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	120094
Description	Brad M23 Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 22-18 AWG, PUR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Brad M23
Protocol	N/A
Type	Single Ended
UPC	883906319571

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	63V AC/DC

Physical

Cable Diameter	9.40mm (.370")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	M23
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	None

LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	76.862/g
Orientation	Straight to Pigtail
Poles	12
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	18, 22

This document was generated on Sep 25, 2025

Obsolete