
TE Connectivity: Every Connection Counts
© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

HARNESSING

HEAT SHRINK BOOTS



✔ Active

TE CONNECTIVITY (TE)

202A185-3/42-0

Raychem | CAP , CRPS

202A185-3/42-0
TE Internal Number: 814730-000
Alias ID: 1-1196347-4

EU RoHS Compliant
EU ELV Compliant

Lipped No

Operating Temperature Range (°C) -20 – 60

Fluid/Chemical Resistance Suitable for occasional exposure to fluids

Adhesive Options /42 Precoat, -20 – 60°C (-4 – 140°F)

Material Systems Code 10

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Boot, Straight, Overexpanded
PDF
English

Product Environmental Compliance

Safety Data Sheet

Aliphatic Polyamide Based Adhesives.
PDF
Dutch

Aliphatic Polyamide Based Adhesives.
PDF
English

Aliphatic Polyamide Based Adhesives.

Downloaded from Arrow.com.

PDF

French

Aliphatic Polyamide Based Adhesives.

PDF

German

Aliphatic Polyamide Based Adhesives.

PDF

Italian

Aliphatic Polyamide Based Adhesives.

PDF

Spanish

Aliphatic Polyamide Based Adhesives.

PDF

Swedish

Aliphatic Polyamide Based Adhesives.

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

FEATURES

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped No

Body Features

Material Systems Code 10
Adhesive Pre-Coat Yes
Material Modified Polyolefin

Dimensions

Cable Diameter Range 19.6 – 54.1 mm [.772 – 2.13 in]
Wire/Cable Outside Diameter .87 in, .9 in, .94 in, 1 in, 1.02 in, 1.1 in, 1.18 in, 1.26 in, 1.34 in, 1.42 in, 22 mm, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 34 mm, 36 mm

Usage Conditions

Operating Temperature Range (°C) -20 – 60

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No
Approved Standards BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

Other

Fluid/Chemical Resistance Suitable for occasional exposure to fluids
Adhesive Options /42 Precoat, -20 – 60°C (-4 – 140°F)
Adhesive Type General Purpose Pre-Coat Adhesive

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.