

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	13OCT2016	QY	CW
	B	ECR-20-012892	12MAY2021	BS	CW
	B1	ECR-22-129466	15FEB2022	BS	CW
	B2	ECR-25-247977	19JUN2025	SC	RB

NOTES:


1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED
DEGREE OF PROTECTION: IP68 (MATED)

注释:

1. 技术参数:
上壳材料: 铝合金
表面处理: 粉末喷涂
防护等级: IP68(配合)



T1920160150-001	HI6BPR-TGXH-M50	HI6BPR HEIGHTEN HOOD, DIAGONAL LOCKING, TOP ENTRY M50, POWDER COATED, BLACK HI6BPR加高上壳, 对角锁定, 顶出M50, 黑色粉末喷涂	M50X1.5
T1920160163-001	HI6BPR-TGXH-M63	HI6BPR HEIGHTEN HOOD, DIAGONAL LOCKING, TOP ENTRY M63, POWDER COATED, BLACK HI6BPR加高上壳, 对角锁定, 顶出M63, 黑色粉末喷涂	M63X1.5
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD-1 PG/M 螺纹孔-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN QIANG YUAN CHK KYLE ZENG APVD CHRIS WANG		13OCT2016 13OCT2016 13OCT2016		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HI6BPR-TGXH-PG/M			
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-137014		SIZE A3	
MATERIAL - -		FINISH - -		APPLICATION SPEC 114-137014		CAGE CODE -	
				WEIGHT -		DRAWING NO C-T19201601XX001	
				CUSTOMER DRAWING		RESTRICTED TO -	
						SCALE 1:2	
						SHEET 1 OF 1	
						REV B2	