

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	9/7/11	
A	Updated Note 1, material was BeCu; Deleted Note 2.	2/18/15	

NOTES:

- OUTER CONDUCTOR AND BODY — BRASS, NICKEL PLATED.
CENTER CONDUCTOR — BRASS AND PHOS. BRONZE, GOLD PLATED.
DIELECTRIC — (TEF) FLUOROCARBON.
- n/a
- SPECIFICATIONS:

FREQUENCY RANGE — DC TO 4 GHz.


ATTENUATION ACCURACY — 0 TO 6 dB ± 0.3 dB.
7 TO 20 dB ± 0.5 dB.
21 TO 30 dB ± 0.75 dB.

VSWR (MAX) — DC TO 4 GHz 1.25:1.

POWER — 2 W (AVG.) @ 25° C DERATED LINEARLY TO 0.5 W @ 125° C
250 W (PEAK) 5 μ s PULSE WIDTH, 0.05% DUTY CYCLE.

IMPEDANCE — 50 Ω ± 1 Ω TYP.

OPERATING TEMPERATURE: —65° C TO +125° C.
TEMPERATURE COEFFICIENT: 10–4 dB/dB/°C.



MODEL NUMBER
CT3369A–XX

ATTENUATION (dB): 03 — 3 dB
06 — 6 dB
08 — 8 dB
10 — 10 dB
14 — 14 dB
20 — 20 dB
30 — 30 dB

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS $\pm 1/32$.XX $\pm .02$ XXX $\pm .005$ DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS	DATE	TITLE ATTENUATOR, FIXED, BNC MALE TO FEMALE, 50Ω			
		FINISH		DRAWN WDH	9/7/11				
NEXT ASSY		USED ON		CHECKED		SIZE A	CAGE CODE 43F45	DWG. NO. P3369A0	REV. A
APPLICATION				ENGR.		SCALE 1:1		SHEET 1 OF 1	
				DESIGN ACTIVITY					