

MICRO SWITCH
a Honeywell Division


FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

YA-2RQ1250-A2

ADG9219




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\phi .139$ MAX ON $1.000 \pm .002$ CENTERS
- 2 - HIGH TEMPERATURE PHENOLICS
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 14 - 22 OZ	CONTACT ARRANGEMENT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE ----- 10 OZ MIN	S P N O		
DIFFERENTIAL TRAVEL ----- .002 - .0075	L23 20A 125, 250 OR 480 VAC	ONE PLACE (.0) $\pm .030$	
OVERTRAVEL ----- .219 MIN	10A 125 VAC "L"	TWO PLACE (.00) $\pm .015$	
	1HP 125 VAC, 2HP 250 VAC	THREE PLACE (.000) $\pm .005$	
	1/2A 125 VDC, 1/4A 250 VDC	ANGLES $\pm$	
	L288	WEIGHT	
	L308		
	L315		
	L319		
	20(3)A 250V $\sim$ T85 5E4		



CATALOG LISTING
YA-2RQ1250-A2
PAGE 1 OF 1

ISSUE
5

REVISIONS

A	207614	CSL	10 MAR 03	01 OCT 09	CMH
B	207734	CSL	24 MAR 03		
C	0017742	TSG	09 JAN 06		
D	0057238	SSK	01 OCT 09		

REPLACES X114681-YA

RELEASE NO. 207278

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

RASTER
DRAWN