



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### General ordering data

|            |                                |
|------------|--------------------------------|
| Version    | Test adapter (terminal), 230 V |
| Order No.  | <a href="#">0299600000</a>     |
| Type       | PS 4 F.STB 4                   |
| GTIN (EAN) | 4008190074043                  |
| Qty.       | 20 items                       |

## PS 4 F.STB 4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 42 mm  | Depth (inches)  | 1.6535 inch |
| Height     | 7.7 mm | Height (inches) | 0.3031 inch |
| Width      | 7.7 mm | Width (inches)  | 0.3031 inch |
| Net weight | 3.16 g |                 |             |

## Temperatures

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Ambient temperature              | -5 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C        |                                  |        |

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 8d191f1d-272c-40a1-8319-7de6fe5d9746 |

## Material data

|                           |              |        |     |
|---------------------------|--------------|--------|-----|
| Basic material            | Polyamide 66 | Colour | red |
| UL 94 flammability rating | V-2          |        |     |

## System specifications

|         |           |
|---------|-----------|
| Version | Test plug |
|---------|-----------|

## Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| With snap-in pegs   | No              | Type of fixing   | Plugged |
| Installation advice | Direct mounting | Type of mounting | Plugged |

## Conductors for clamping (rated connection)

|                                                      |                   |                                                      |                     |
|------------------------------------------------------|-------------------|------------------------------------------------------|---------------------|
| Stripping length                                     | 5 mm              | Type of connection                                   | Plug-in connection  |
| Wire connection cross section, finely stranded, max. | 4 mm <sup>2</sup> | Wire connection cross section, finely stranded, min. | 0.5 mm <sup>2</sup> |
| Connection cross-section, stranded, max.             | 4 mm <sup>2</sup> |                                                      |                     |

## Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 7.70 mm |
|-----------------|---------|

## General

|                                   |        |                     |                 |
|-----------------------------------|--------|---------------------|-----------------|
| Number of poles                   | 1      | Installation advice | Direct mounting |
| Operating temperature range, max. | 100 °C |                     |                 |

## Rating data

|               |       |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002555    | ETIM 7.0    | EC002555    |
| ETIM 8.0    | EC002555    | ETIM 9.0    | EC002555    |
| ETIM 10.0   | EC002555    | ECLASS 9.0  | 27-14-11-48 |
| ECLASS 9.1  | 27-14-11-48 | ECLASS 10.0 | 27-14-11-48 |
| ECLASS 11.0 | 27-14-11-48 | ECLASS 12.0 | 27-14-11-48 |
| ECLASS 13.0 | 27-25-03-04 | ECLASS 14.0 | 27-25-03-04 |
| ECLASS 15.0 | 27-25-03-04 |             |             |