

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**







To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

| Version    | Feed-through terminal block, Screw connection,<br>beige, 4 mm <sup>2</sup> , 32 A, 800 V, Number of connec-<br>tions: 2 |
|------------|---|
| Order No.  | <u>9502600000</u>   |
| Туре       | SAKK 4  |
| GTIN (EAN) | 4008190550585   |
| Qty.       | 25 pc(s).   |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| -   |         |     |         |
|-----|---------|-----|---------|
| Dim | ensions | and | weights |
|     |         |     |         |

| Depth      | 53 mm   | Depth (inches)  | 2.087 inch |
|------------|---------|-----------------|------------|
| Height     | 40 mm   | Height (inches) | 1.575 inch |
| Width      | 8 mm    | Width (inches)  | 0.315 inch |
| Net weight | 30.14 g |                 |            |

## **Temperatures**

| Storage temperature              | -25 °C55 °C | Ambient temperature              | -5 °C40 °C |
|----------------------------------|-------------|----------------------------------|------------|
| Continuous operating temp., min. | -60 °C      | Continuous operating temp., max. | 250 °C     |

#### **Material data**

| Material                  | Ceramic  | Colour | beige |
|---------------------------|----------|--------|-------|
| UL 94 flammability rating | V-0. 5VB |        |       |

## **Rating data IECEx/ATEX**

| Certificate No. (ATEX)         | TUEV18ATEX8208U | Certificate No. (IECEX)         | IECEXTUR18.0018U |
|--------------------------------|-----------------|---------------------------------|------------------|
| Max. voltage (ATEX)            | 440 V           | Current (ATEX)                  | 32 A             |
| Wire cross section max. (ATEX) | 6 mm²           | Max. voltage (IECEX)            | 440 V            |
| Current (IECEX)                | 32 A            | Wire cross section max. (IECEX) | 6 mm²            |
| Marking EN 60079-7             | Ex eb II C Gb   | Ex 2014/34/EU label             | II 2 G D         |

## **System specifications**

| Version                             | Screw connection, for scre-<br>wable cross-connection,<br>One end without connec- | End cover plate required      |     |
|-------------------------------------|---|-------------------------------|-----|
|                                     | tor   |                               | Yes |
| Number of potentials                | 1   | Number of levels              | 1   |
| Number of clamping points per level | 2   | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No  | PE connection                 | No  |
| Rail                                | TS 32   | N-function                    | No  |
| PE function                         | No  | PEN function                  | No  |

## **Additional technical data**

| Explosion-tested version    | Yes     | Installation advice | Direct mounting |
|-----------------------------|---------|---------------------|-----------------|
| Number of similar terminals | 1       | Open sides          | right           |
| Type of mounting            | Snap-on |                     |                 |

## **CSA** rating data

| Certificate No. (CSA)         | 12400-290 | Current size C (CSA)          | 36 A   |
|-------------------------------|-----------|-------------------------------|--------|
| Voltage size C (CSA)          | 600 V     | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG    |                               |        |

## **Conductors for clamping (additional connection)**

Connection type, additional connection Screw connection



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

## **Conductors for clamping (rated connection)**

| , 3,   |                      |  |                   |
|--|----------------------|--|-------------------|
| Blade size   | 0.6 x 3.5 mm         | Clamping range, max.   | 6 mm <sup>2</sup> |
| Clamping range, min.   | 0.33 mm <sup>2</sup> | Clamping screw   | M 3               |
| Connection cross-section, stranded,  | 0.00 111111          | Connection cross-section, stranded, mir  |                   |
| max.   | 4 mm <sup>2</sup>    |  | 0.5 mm²           |
| Connection direction   | on side              | Gauge to IEC 60947-1   | A4                |
| Number of connections  | 2                    | Stripping length   | 10 mm             |
| Tightening torque, max.  | 0.5 Nm               | Tightening torque, min.  | 0.5 Nm            |
| Type of connection   |                      | Wire connection cross section AWG,   |                   |
|  | Screw connection     | max.   | AWG 10            |
| Wire connection cross section AWG,   |                      | Wire connection cross section, finely  |                   |
| min.   | AWG 22               | stranded, max.   | 4 mm <sup>2</sup> |
| Wire connection cross section, finely  |                      | Wire connection cross-section, fine-   |                   |
| stranded, min.   | 0 E2                 | ly stranded with wire-end ferrules DIN   | 42                |
| Wire connection organ section for  | 0.5 mm <sup>2</sup>  | 46228/1, max.  | 4 mm <sup>2</sup> |
| Wire connection cross-section, fine-<br>ly stranded with wire-end ferrules DIN |                      | Wire connection cross-section, fine-<br>ly stranded with wire-end ferrules DIN |                   |
| 46228/1, min.  | 0.5 mm <sup>2</sup>  | 46228/4, max.  | 4 mm <sup>2</sup> |
| Wire connection cross-section, fine-   |                      | Wire connection cross-section, solid   |                   |
| ly stranded with wire-end ferrules DIN   |                      | core, max.   |                   |
| 46228/4, min.  | 0.5 mm <sup>2</sup>  |  | 6 mm <sup>2</sup> |
| Wire connection cross-section, solid   |                      |  |                   |
| core, min.   | 0.5 mm <sup>2</sup>  |  |                   |
| General  |                      |  |                   |
| Installation advice  | Direct mounting      | Rail   | TS 32             |
| Standards  | Direct mounting      | Wire connection cross section AWG.   | 13 32             |
| Statidalus   | IEC 60947-7-1        | max.   | AWG 10            |
| Wire connection cross section AWG,   |                      |  |                   |
| min.   | AWG 22               |  |                   |
| Rating data  |                      |  |                   |
|  |                      |  |                   |
| Rated cross-section  | 4 mm <sup>2</sup>    | Rated voltage  | 800 V             |
| Rated DC voltage   | 800 V                | Rated current  | 32 A              |
| Current at maximum wires   | 41 A                 | Standards  | IEC 60947-7-1     |
| Volume resistance according to IEC   |                      | Rated impulse withstand voltage  |                   |
| 60947-7-x  | 1 mΩ                 |  | 8 kV              |
| Power loss in accordance with IEC<br>60947-7-x                                 | 1.02 W               | Pollution severity   | 3                 |
| UL rating data   |                      |  |                   |
|  |                      |  |                   |
| Certificate No. (UR)   | E60693               | Conductor size Factory wiring max. (UR)  | 12 AWG            |
| Conductor size Factory wiring min. (UR)  |                      | Conductor size Field wiring max. (UR)  | 12 AWG            |
| Conductor size Field wiring min. (UR)  | 26 AWG               | Current size C (UR)  | 30 A              |
| Voltage size C (UR)  | 600 V                |  |                   |
| Classifications  |                      |  |                   |
|  |                      |  |                   |
| ETIM 6.0   | EC000897             | ETIM 7.0   | EC000897          |
| ETIM 8.0   | EC000897             | ETIM 9.0   | EC000897          |
| ETIM 10.0  | EC000897             | ECLASS 9.0   | 27-14-11-20       |
| ECLASS 9.1   | 27-14-11-20          | ECLASS 10.0  | 27-14-11-20       |
| FOLACC 11 O  | 07 14 14 00          | FOLACC 10.0  | 07 14 14 00       |

ECLASS 12.0

ECLASS 14.0

Creation date May 23, 2025 12:45:04 AM CEST

27-14-11-20

27-25-01-01

27-25-01-01

27-14-11-20

27-25-01-01

ECLASS 11.0

ECLASS 13.0

ECLASS 15.0



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

#### **Environmental Product Compliance**

| RoHS Compliance Status | Compliant without exemption |
|------------------------|-----------------------------|
| REACH SVHC             | No SVHC above 0.1 wt%       |

#### **Approvals**

Approvals





| Approvals MAMID           | https://mdcop.weidmueller.com/mediadelivery/rendition/900_319217/-T1z1mm-S800/ https:// |
|---------------------------|---|
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319231/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319240/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319244/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319213/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/ https://         |
|                           | mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/                  |
| ROHS                      | Conform   |
| UL File Number Search     | UL Website  |
| Certificate No. (UR)      | E60693  |
| Certificate No. (cURusEX) | E184763   |
|                           |   |

#### **Downloads**

| Approval/Certificate/Document of Con- | Attestation Of Conformity              |
|---------------------------------------|--|
| formity                               | ATEX Certificate                       |
|                                       | IECEx Certificate                      |
|                                       | <u>CB Certificate</u>                  |
|                                       | CB Test Certificate                    |
|                                       | CCC Ex Certificate                     |
|                                       | Declaration of Conformity              |
|                                       | UKCA declaration of conformity         |
| Engineering Data                      | CAD data – STEP                        |
| Product Change Notification           | PCN_SAKK_20190405                      |
| User Documentation                    | NTI SAKK 4                             |
|                                       | <u>StorageConditionsTerminalBlocks</u> |
| Catalogues                            | Catalogues in PDF-format               |
|                                       |  |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

#### **SAK-Series**

SAK Series End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

### **General ordering data**

Туре AP SAKK4/10 KER/WS

Order No. 9502630000

GTIN (EAN) 4008190047290

Qty. 10 pc(s).

End plate for terminals, white, Height: 40 mm, Width: 3 mm, V-0,

Ceramic, Snap-on: Yes

#### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

Туре DEK 5/5 MC SDR Version Order No. 1609810000 Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

GTIN (EAN) 4008190456597

Weidmueller, To customer specification

200 pc(s).

Qty.



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

#### **QL** mounting screws



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

### **General ordering data**

Туре KISC M3X20.5/10 EK4 Order No. 0303000000 GTIN (EAN)

4008190163686

Qty. 100 pc(s).

Clamping yoke, Mounting screw, Steel

#### Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

| Туре              | DEK 5/6.5 PLUS MC NE GE               | Version   |
|-------------------|---------------------------------------|---|
| Order No.         | 1364020000                            | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50         |
| GTIN (EAN)        | 4050118166057                         | Weidmueller, yellow   |
| Qty.              | 900 pc(s).                            |   |
|                   |                                       |   |
| Туре              | DEK 5/6.5 PLUS MC NE WS               | Version   |
| Type<br>Order No. | DEK 5/6.5 PLUS MC NE WS<br>1046340000 | Version Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
|                   | ,                                     |   |

Creation date May 23, 2025 12:45:04 AM CEST



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw. The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## **General ordering data**

| Туре       | SCHT 7        | Version   |
|------------|---------------|---|
| Order No.  | 0517960000    | SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00 |
| GTIN (EAN) | 4008190001742 | Weidmueller, white  |
| Qty.       | 20 pc(s).     |   |

## QL / SAKK 4



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

| Туре              | QL 4 SAKK4               | Version  |
|-------------------|--------------------------|--|
| Order No.         | <u>9502560000</u>        | Cross-connector (terminal), when screwed in, grey, 32 A, Number of         |
| GTIN (EAN)        | 4008190550554            | poles: 4, Pitch in mm (P): 8.00, Insulated: No, Width: 29.7 mm             |
| Qty.              | 50 pc(s).                |  |
|                   |                          |  |
| Type              | QL 2 SAKK4               | Version  |
| Type<br>Order No. | OL 2 SAKK4<br>9502540000 | Version Cross-connector (terminal), when screwed in, grey, 32 A, Number of |
|                   |                          |  |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

•

## **Accessories**

### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## **General ordering data**

| Туре              | DEK 5/6.5 MC SDR                    | Version  |
|-------------------|-------------------------------------|--|
| Order No.         | 1609850000                          | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50            |
| GTIN (EAN)        | 4008190456610                       | Weidmueller, To customer specification                                 |
| Qty.              | 180 pc(s).                          |  |
|                   |                                     |  |
| Туре              | DEK 5/6.5 PLUS MC SDR               | Version  |
| Type<br>Order No. | DEK 5/6.5 PLUS MC SDR<br>1046360000 | Version<br>Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
|                   | ,                                   |  |

## **Connection sleeves**



| Туре       | VH 13.5/4.9/3.3 NI | Version   |
|------------|--------------------|---|
| Order No.  | 9502580000         | Connecting sleeve (terminal), when screwed in, Width: 4.9 mm, |
| GTIN (EAN) | 4008190550578      | Height: 13.5 mm, Depth: 4.9 mm, Number of poles: 1, Cu Zn     |
| Qty.       | 100 pc(s).         |   |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

#### **TS 32**

**TS 32** 

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

#### General ordering data

Туре MEW 1/32 Order No. 0445600000 GTIN (EAN) 4008190178093

20 pc(s).

End bracket, grey, TS 32, None, Steel, Width: 10.5 mm, 100 °C

#### **Blank**

Qty.



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

Туре DEK 5/5 MC NE WS Version Order No. 1609801044 Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 GTIN (EAN) 4008190397111 Weidmueller, white 1,000 pc(s). Qty.



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

#### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- · Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

DEK 5/6.5 MC NE WS Order No. 1609840000 GTIN (EAN) 4008190203429 Qty. 900 pc(s).

Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50

Weidmueller, white

### Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

| Туре              | BZT 1 ZA WS 10/5            | Version                            |
|-------------------|-----------------------------|------------------------------------|
| Order No.         | 1805520000                  | Accessories, Marker holder         |
| GTIN (EAN)        | 4032248270248               |                                    |
| Qty.              | 100 pc(s).                  |                                    |
|                   |                             |                                    |
| Туре              | BZT 1 WS 10/5               | Version                            |
| Type<br>Order No. | BZT 1 WS 10/5<br>1805490000 | Version Accessories, Marker holder |
|                   | · ·                         |                                    |