







LAY-OUT P.C.B.- HOLE



PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5 A AT 20°C (FULLY LOADED)

1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE 500V AC (CONT / CONT)

OPERATING TEMPERATURE -55°C TO 125°C

CONTACT RESISTANCE 20 MΩ MAX

INSERTION FORCE :0.75 N MAX /CONT

EXTRACTION FORCE: 0.15 N MIN /CONT

INSULATION RESISTANCE :10⁴ MΩ MIN

NOTES

1. PART NUMBER DESCRIPTION:

HM2R10PA5100--C--

LEAD FREE INDICATOR:

LF: LEAD FREE

PERFORMANCE LEVEL INDICATOR

(REF DWG No. BS,C,201844,003)

2. THIS PRODUCT IS CSA APPROVED

THIS PRODUCT IS UL RECOGNISED

3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING: BSA,201,572001

4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004

mat'l. code				surface	tolerance	projection	product family			
—				ISO 1302	ISO 406 ISO 1101		MILLIPACS			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
A	DG05-0262	Guo JM	2005-08-05	angles	linear		MPACS 5+2R RA RCP CONN TYPE A			
B	DG07-0362	Kason	2007-09-05			MM				
C	DG10-0110	NZ	2010-03-22	0°±1°		scale				
D	DG-004068-1	TER	2011-07-25	dr	Kason Luo	2005-08-03	dwg no		sheet 1 of 1	size
E	ELX-I-37072	MINI	2020-05-18	enr	Collins Lu	2005-08-03	BS, C ,201419 ,025		A3	5
				chr	BINESH	2020-05-18				
				appd	SANOJ	2020-05-18				
sheet index		revision	E				type		Product Customer	Drawing
		sheet	1							