



Modules for industrial use

LCD Product Brief | NL10276BC13-01C

6.5", XGA, TN (T-EVT), HIGH BRIGHTNESS, REPLACABLE BACKLIGHT

Part number	NL10276BC13-01C
Screen size in inch	6.5"
Resolution in pixels (Horizontal x Vertical)	1024x768
Graphic Mode	XGA
Panel technology	TN
Display type	TN (T-EVT)
Replacement Backlight	65LHS13
Color gamut	36%
Luminance in cd/m ²	650
Contrast	500:1
Viewing angle in °: Up/down/right/left	80,60,80,80
Surface	AR+Clear
Response time (rise + fall) in ms	25
Interface	LVDS 6/8b
LED lifetime in Khours	16
Storage temperature in °C	-30~80
Operating temperture in °C	-20~70
Outline dimension (Width x Height x Thickness) in mm	153.0 x 118.0 x 9.0
Weight in g	170
Remark	T-EVT